



# BEF-KHS-N03N

Brackets

**MOUNTING SYSTEMS**

**SICK**  
Sensor Intelligence.



### Ordering information

| Type         | part no. |
|--------------|----------|
| BEF-KHS-N03N | 2051619  |

**Included in delivery:** BEF-KHS-KH3N (1)

Other models and accessories → [www.sick.com/Brackets](http://www.sick.com/Brackets)

### Detailed technical data

#### Features


|                             |   |
|-----------------------------|---|
| <b>Accessory group</b>      | Mounting systems  |
| <b>Accessory family</b>     | Brackets  |
| <b>Description</b>          | Plate N03N for universal clamp bracket  |
| <b>Material</b>             | Stainless steel 1.4571 (sheet), Stainless steel 1.4408 (clamp)  |
| <b>Items supplied</b>       | Universal clamp (5322627), mounting hardware  |
| <b>Usable for</b>           | UC12<br>W14-2<br>W18-2<br>W18-3<br>W11-2<br>W12-3<br>W12-2 Laser<br>W12G<br>W12 Teflon<br>W16<br>W24-2 Ex<br>PowerProx<br>W11G-2<br>TranspaTect<br>W18-3 Ex<br>W24-2<br>PL50A<br>PL80A<br>PL40A<br>P250 |
| <b>Mounting system type</b> | Mounting plate  |

#### Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27279202 |
| <b>ECLASS 5.1.4</b> | 27279202 |
| <b>ECLASS 6.0</b>   | 27279202 |
| <b>ECLASS 6.2</b>   | 27279202 |
| <b>ECLASS 7.0</b>   | 27279202 |
| <b>ECLASS 8.0</b>   | 27279202 |
| <b>ECLASS 8.1</b>   | 27279202 |
| <b>ECLASS 9.0</b>   | 27273701 |


|                       |          |
|-----------------------|----------|
| <b>ECLASS 10.0</b>    | 27273701 |
| <b>ECLASS 11.0</b>    | 27273701 |
| <b>ECLASS 12.0</b>    | 27273701 |
| <b>ETIM 5.0</b>       | EC002024 |
| <b>ETIM 6.0</b>       | EC002024 |
| <b>ETIM 7.0</b>       | EC002024 |
| <b>ETIM 8.0</b>       | EC002024 |
| <b>UNSPSC 16.0901</b> | 32131023 |

Dimensional drawing



Dimensions in mm (inch)


### Dimensional drawing



Dimensions in mm (inch)  
BEF-KHS-KH3

### Recommended accessories

Other models and accessories → [www.sick.com/Brackets](http://www.sick.com/Brackets)

|   | Brief description   | Type         | part no. |
|---|---|--------------|----------|
| Mounting systems  |   |              |          |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Mounting bar, straight, 300 mm, stainless steel</li> <li><b>Material:</b> Stainless steel</li> <li><b>Details:</b> Stainless steel (1.4571)</li> </ul> | BEF-MS12G-NB | 4058915  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)