



# YF2A28-C15S01XY2C4

Y- and T-splitters

CONNECTORS AND CABLES

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
YF2A28-C15S01XY2C4	2122940

Other models and accessories → [www.sick.com/Y\\_and\\_T-splitters](http://www.sick.com/Y_and_T-splitters)



### Detailed technical data




#### Technical specifications

<b>Connection type head A</b>	Female connector, M12, 8-pin, A-coded
<b>Connection type head B</b>	Female connector, M12, 4-pin, D-coded
<b>Connection type head C</b>	Male connector, M12, 4-pin, A-coded
<b>Locking plug connector</b>	Screw connection
<b>Connecting cable</b>	0.15 m, 4-wire, PUR, halogen-free
<b>Cable material</b>	PUR, halogen-free
<b>Conductor cross section</b>	0.34 mm <sup>2</sup>
<b>Connector material head A</b>	TPU
<b>Connector material head C</b>	TPU
<b>Locking nut material</b>	Zinc die-cast, nickel-plated
<b>Width across flats</b>	13
<b>Tightening torque</b>	0.6 Nm
<b>Shielding, head</b>	Shielded
<b>Shielding</b>	Shielded
<b>Reference voltage</b>	≤ 30 V DC
<b>Rated impulse voltage</b>	0.8 kV
<b>Contamination rating</b>	3
<b>Overvoltage category</b>	III
<b>Bending radius</b>	
Stationary position	> 5 x cable diameter
<b>Operating temperature</b>	
Flexible use	-25 °C ... +80 °C
Stationary position	-40 °C ... +80 °C
Head	-25 °C ... +85 °C

#### Certificates

<b>EU declaration of conformity</b>	✓
<b>China RoHS</b>	✓

Dimensional drawing



Dimensions in mm (inch)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)