



# PM3S11-00330030

Mirror

REFLECTORS AND OPTICS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
PM3S11-00330030	1040625

Other models and accessories → [www.sick.com/Mirror](http://www.sick.com/Mirror)

### Detailed technical data

#### Features

<b>Mounting system type</b>	Mechanical anchoring to the floor
<b>Mirror height</b>	90 mm
<b>Mirror width</b>	100 mm
<b>Suitable for</b>	Safety multibeam sensors
Suitable for number of beams	3
Suitable for beam separation	400 mm
<b>Type of diversion</b>	Horizontal

#### Mechanics


<b>Dimensions</b>	
L1	300 mm
L2	400 mm
L3	400 mm
L5	1,185 mm
<b>Weight</b>	+ 6,600 g

#### Classifications

<b>ECLASS 5.0</b>	27279207
<b>ECLASS 5.1.4</b>	27279207
<b>ECLASS 6.0</b>	27279207
<b>ECLASS 6.2</b>	27279207
<b>ECLASS 7.0</b>	27279207
<b>ECLASS 8.0</b>	27279207
<b>ECLASS 8.1</b>	27279207
<b>ECLASS 9.0</b>	27273605
<b>ECLASS 10.0</b>	27273605
<b>ECLASS 11.0</b>	27273605
<b>ECLASS 12.0</b>	27273605
<b>ETIM 5.0</b>	EC002467

<b>ETIM 6.0</b>	EC002467
<b>ETIM 7.0</b>	EC002467
<b>ETIM 8.0</b>	EC002467
<b>UNSPSC 16.0901</b>	39111609

Dimensional drawing PM3S mirror column for horizontal beam deflection. Note the reduced scanning range!



Type	Part no.	Suitable for number of beams	Suitable for beam separation	L1 = Height of lowest beam from the floor	L2 = Beam separation	L3 = Beam separation	L4 = Beam separation	L5 = Column height (incl. base plate)
PM3S96-0024002	1040619	2	500	400 (15.75)	500 (19.69)	-	-	985 (38.78)

Type	Part no.	Suitable for number of beams	Suitable for beam separation	L1 = Height of lowest beam from the floor	L2 = Beam separation	L3 = Beam separation	L4 = Beam separation	L5 = Column height (incl. base plate)
PM3S96-0023006	1040620	2	600	300 (11.81)	600 (23.62)	-	-	985 (38.78)
PM3S11-0033003	1040625	3	400	300 (11.81)	400 (15.75)	400 (15.75)	-	1,185 (46.65)
PM3S13-0033005	1040624	3	450	300 (11.81)	450 (17.72)	450 (17.72)	-	1,285 (50.59)
PM3S13-0043004	1040626	4	300	300 (11.81)	300 (11.81)	300 (11.81)	300 (11.81)	1,285 (50.59)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)