



CDB730-001  
CDB

JUNCTION BOXES

**SICK**  
Sensor Intelligence.



Illustration may differ



## Ordering information

Type	part no.
CDB730-001	1055981

Other models and accessories → [www.sick.com/CDB](http://www.sick.com/CDB)

## Detailed technical data

### Features

<b>Brief description</b>	Small connection module for one sensor, 4 cable glands (only for TiM3xx-10xxxxx)
<b>Supported products</b>	TiM3xx
<b>Cloning module support (CMC)</b>	No
<b>Supports display module (CMD)</b>	No
<b>Supports power supply module (CMP)</b>	No
<b>Supports fieldbus gateway (CMF)</b>	No

### Mechanics/electronics

<b>Power consumption</b>	1 W
<b>Housing</b>	Polycarbonate
<b>Enclosure rating</b>	IP65 (DIN 40 050) <sup>1)</sup>
<b>Protection class</b>	III
<b>Weight</b>	+ 250 g
<b>Dimensions (L x W x H)</b>	124.2 mm x 113.1 mm x 53.9 mm
<b>Scanner connection</b>	15-pin D-Sub HD female connector

<sup>1)</sup> When using a standard connection cable for scanners by SICK.

### Interfaces

<b>Digital inputs</b>	Depending on sensor connected
<b>Digital outputs</b>	Depending on sensor connected
<b>Optical indicators</b>	9 LEDs
<b>Configuration software</b>	SOPAS ET

### Ambient data

<b>Ambient operating temperature</b>	0 °C ... +40 °C
<b>Storage temperature</b>	-20 °C ... +70 °C
<b>Permissible relative humidity</b>	± 90 %, Non-condensing

### Certificates


<b>EU declaration of conformity</b>	✓
-------------------------------------	---

<b>UK declaration of conformity</b>	✓
<b>ACMA declaration of conformity</b>	✓
<b>China RoHS</b>	✓

## Classifications

<b>ECLASS 5.0</b>	27242208
<b>ECLASS 5.1.4</b>	27242608
<b>ECLASS 6.0</b>	27242608
<b>ECLASS 6.2</b>	27242608
<b>ECLASS 7.0</b>	27242608
<b>ECLASS 8.0</b>	27242608
<b>ECLASS 8.1</b>	27242608
<b>ECLASS 9.0</b>	27242608
<b>ECLASS 10.0</b>	27242608
<b>ECLASS 11.0</b>	27242608
<b>ECLASS 12.0</b>	27242608
<b>ETIM 5.0</b>	EC001604
<b>ETIM 6.0</b>	EC001604
<b>ETIM 7.0</b>	EC001604
<b>ETIM 8.0</b>	EC001604
<b>UNSPSC 16.0901</b>	32151705


## Dimensional drawing CDB620



Dimensions in mm (inch)

Recommended accessories

Other models and accessories → [www.sick.com/CDB](http://www.sick.com/CDB)

	Brief description	Type	part no.
integration modules and adapters			
	<ul style="list-style-type: none"><li><b>Description:</b> External parameter memory for integration in CDB620/CDB650/CDM42x</li></ul>	CMC600-101	1042259

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)