



BEF-EL-G34D20-FTMG

Assembly accessories

MOUNTING SYSTEMS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
BEF-EL-G34D20-FTMG	2111052

Other models and accessories → www.sick.com/Assembly_accessories

Detailed technical data


Features

Accessory group	Mounting systems
Accessory family	Assembly accessories
Description	Flow Conditioning Pipes for FTMg (FTMG-xxx20xxx) with process connection G3/4 in 1.4305

Classifications

ECLASS 5.0	27279202
ECLASS 5.1.4	27279202
ECLASS 6.0	27279202
ECLASS 6.2	27279202
ECLASS 7.0	27279202
ECLASS 8.0	27279202
ECLASS 8.1	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ETIM 5.0	EC002024
ETIM 6.0	EC002024
ETIM 7.0	EC002024
ETIM 8.0	EC002024
UNSPSC 16.0901	32131023

Dimensional drawing



Dimensions in mm (inch)

Type	L1	L2	L3	D1	D2	Width across flats
BEF-EL-G14D08-FTMG	110 (4.33)	44 (1.73)	20 (0.79)	Ø 14 (Ø 0.55)	G 1/4	24
BEF-EL-R14D08-FTMG	110 (4.33)	44 (1.73)	19,5 (0.77)	Ø 14 (Ø 0.55)	R 1/4	24
BEF-EL-N14D08-FTMG	110 (4.33)	44 (1.73)	13,2 (0.52)	Ø 14 (Ø 0.55)	1/4" NPT	24
BEF-EL-G12D15-FTMG	161 (6.34)	80,5 (3.17)	22 (0.87)	Ø 22,2 (Ø 0.87)	G 1/2	32
BEF-EL-R12D15-FTMG	161 (6.34)	80,5 (3.17)	20 (0.79)	Ø 22,2 (Ø 0.87)	R 1/2	32
BEF-EL-N12D15-FTMG	161 (6.34)	80,5 (3.17)	24,1 (0.95)	Ø 22,2 (Ø 0.87)	1/2" NPT	32
BEF-EL-G34D20-FTMG	217 (8.54)	108,5 (4.27)	22 (0.87)	Ø 27,5 (Ø 1.08)	G 3/4	39
BEF-EL-R34D20-FTMG	217 (8.54)	108,5 (4.27)	20 (0.79)	Ø 27,5 (Ø 1.08)	R 3/4	39
BEF-EL-N34D20-FTMG	217 (8.54)	108,5 (4.27)	24,1 (0.95)	Ø 27,5 (Ø 1.08)	3/4" NPT	39
BEF-EL-G10D25-FTMG	273 (10.75)	136,5 (5.37)	25 (0.98)	Ø 34 (Ø 1.34)	G 1	48
BEF-EL-R10D25-FTMG	273 (10.75)	136,5 (5.37)	20 (0.79)	Ø 34 (Ø 1.34)	R 1	48
BEF-EL-N10D25-FTMG	273 (10.75)	136,5 (5.37)	24,1 (0.95)	Ø 34 (Ø 1.34)	1" NPT	48

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com