



Optics protection hood (PMMA) - for white, red illumination

Lenses

REFLECTORS AND OPTICS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
Optics protection hood (PMMA) - for white, red illumination	2141197

Other models and accessories → www.sick.com/Lenses

Detailed technical data

Features

Product segment	Reflectors and optics
Product	Lenses
Product version	Lens accessories
Description	Optics protection hood, PMMA, 46.9 mm, for use with the illumination colors white, red and lenses with a focal length of 8 mm (part. no. 5349682), 12 mm (part. no. 5342133), 16 mm (part. no. 5342134) or 25 mm (part. no. 5342135)
Suitable for	Lector83x, Inspector83x, Lector83x, Inspector83x
Material	Plastic (PMMA), 2 mm thick, with scratch-proof, anti-reflection (AR) coating on both sides
Enclosure rating	IP65

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com