



# C-mount lens

Lenses

REFLECTORS AND OPTICS

**SICK**  
Sensor Intelligence.



Illustration may differ

### Ordering information

Type	part no.
C-mount lens	4109783

Other models and accessories → [www.sick.com/Lenses](http://www.sick.com/Lenses)

### Detailed technical data

#### Features

<b>Description</b>	C-Mount lens 1/1.8", focal length 12 mm, lens aperture 1.8 – 11
<b>Lens</b>	
Type of connector	C-mount
Focal length	12 mm
Aperture	1.8 ... 11
<b>Dimensions (W x H x L)</b>	36.5 mm (Without C-mount thread)
<b>Diameter</b>	30 mm

#### Classifications

<b>ECLASS 5.0</b>	27279205
<b>ECLASS 5.1.4</b>	27279205
<b>ECLASS 6.0</b>	27279205
<b>ECLASS 6.2</b>	27279205
<b>ECLASS 7.0</b>	27279205
<b>ECLASS 8.0</b>	27279205
<b>ECLASS 8.1</b>	27279205
<b>ECLASS 9.0</b>	27273603
<b>ECLASS 10.0</b>	27273603
<b>ECLASS 11.0</b>	27273603
<b>ECLASS 12.0</b>	27273603
<b>ETIM 5.0</b>	EC001776
<b>ETIM 6.0</b>	EC001776
<b>ETIM 7.0</b>	EC001776
<b>ETIM 8.0</b>	EC001776
<b>UNSPSC 16.0901</b>	45121603

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)