



C-mount lens

Lenses

REFLECTORS AND OPTICS

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

Type	part no.
C-mount lens	4109796

Other models and accessories → www.sick.com/Lenses

Detailed technical data

Features

Description	C-mount lens 1.1", focal distance 35 mm, aperture 1.8 – 16
Lens	
Type of connector	C-mount
Focal length	35 mm
Aperture	1.8 ... 16
Dimensions (W x H x L)	66 mm (Without C-mount thread)
Diameter	45 mm

Classifications

ECLASS 5.0	27279205
ECLASS 5.1.4	27279205
ECLASS 6.0	27279205
ECLASS 6.2	27279205
ECLASS 7.0	27279205
ECLASS 8.0	27279205
ECLASS 8.1	27279205
ECLASS 9.0	27273603
ECLASS 10.0	27273603
ECLASS 11.0	27273603
ECLASS 12.0	27273603
ETIM 5.0	EC001776
ETIM 6.0	EC001776
ETIM 7.0	EC001776
ETIM 8.0	EC001776
UNSPSC 16.0901	45121603

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com