



SAC-5P-M12Y / 2xM12FS VP

Y- and T-splitters

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SAC-5P-M12Y / 2xM12FS VP	6026517

Other models and accessories → www.sick.com/Y_and_T-splitters



Detailed technical data

Technical specifications

Connection type head A	Male connector, M12, 5-pin, A-coded
Connection type head B	Female connector, M12, 5-pin, A-coded
Connection type head C	Female connector, M12, 5-pin, A-coded
Connector material head A	TPU
Connector material head C	TPU
Housing color	Green
Locking nut material	Zinc diecast, teflon coated (B), zinc die-cast, nickel-plated (C)
Shielding	Unshielded
Reference voltage	≤ 24 V AC, ≤ 24 V DC
Current loading	≤ 4 A
Insulation resistance	≥ 10 Ω
Specific insulation resistance	≤ 5 MΩ
Operating temperature	-25 °C ... +90 °C
Enclosure rating	IP67 ¹⁾
Operating temperature	
	Head -25 °C ... +90 °C

¹⁾ Only in fully locked position with its plugs.

Certificates


EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	27279201
ECLASS 5.1.4	27279201
ECLASS 6.0	27279201
ECLASS 6.2	27279201
ECLASS 7.0	27279201

ECLASS 8.0	27279201
ECLASS 8.1	27279201
ECLASS 9.0	27440108
ECLASS 10.0	27440108
ECLASS 11.0	27440108
ECLASS 12.0	27440108
ETIM 5.0	EC002585
ETIM 6.0	EC002585
ETIM 7.0	EC002585
ETIM 8.0	EC002585
UNSPSC 16.0901	31163032


Dimensional drawing



Dimensions in mm (inch)

Dimensions in mm (inch)

Pinouts



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com