



YF2Z14-100XXXXLEAX

Other connectors and cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
YF2Z14-100XXXXLEAX	6027559

Other models and accessories → www.sick.com/Other_connectors_and_cables



Detailed technical data

Technical specifications

Connection type head A	Female connector, M12, 4-pin, straight	
Connection type head B	Flying leads	
Connection type	Flying leads	
Connector material	TPU	
Connector color	Black	
Locking nut material	Zinc die-cast, nickel-plated	
Tightening torque	0.4 Nm	
Cable	10 m, 4-wire, PUR, halogen-free	
Jacket material	PUR, halogen-free	
Jacket color	Black	
Cable diameter	4.7 mm	
Conductor cross section	0.34 mm ²	
Shielding	Unshielded	
Bending radius		
Flexible use	> 10 x cable diameter	
Stationary position	> 5 x cable diameter	
Bending cycles	≥ 4,000,000	
Reference voltage	≤ 250 V	
Current loading	4 A	
Traversing speed	3 m/s	
Travelling distance	10 m	
Acceleration	≤ 10 m/s ²	
Application	Drag chain operation	
UL File No.	CYJV.E335179	
Enclosure rating	IP65/ IP67/ IP68	
Operating temperature		
Flexible use	-25 °C ... +80 °C	
Stationary position	-40 °C ... +80 °C	

Head -25 °C ... +90 °C

Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com