



SYL-1205-G0M3

Y- and T-splitters

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SYL-1205-G0M3	6043534

Other models and accessories → www.sick.com/Y-_and_T-splitters



Detailed technical data

Technical specifications

Connection type head A	Female connector, M12, 4-pin, A-coded
Connection type head B	Male connector, M12, 3-pin, A-coded
Connection type head C	Male connector, M12, 3-pin, A-coded
Connecting cable	0.3 m, PVC
Cable material	PVC
Conductor cross section	0.34 mm ²
Connector material head A	TPU
Connector material head C	TPU
Locking nut material	Nickel-plated brass
Shielding, head	Unshielded
Shielding	Unshielded
Reference voltage	≤ 250 V DC
Current loading	≤ 4 A
Contamination rating	3
Operating temperature	-40 °C ... +80 °C, stationary position and flexible use
Enclosure rating	IP67
Operating temperature	
Head	-30 °C ... +80 °C

Certificates


EU declaration of conformity	✓
UK declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	27279201
ECLASS 5.1.4	27279201
ECLASS 6.0	27279201
ECLASS 6.2	27279201
ECLASS 7.0	27279201
ECLASS 8.0	27279201


ECLASS 8.1	27279201
ECLASS 9.0	27440108
ECLASS 10.0	27440108
ECLASS 11.0	27440108
ECLASS 12.0	27440108
ETIM 5.0	EC002585
ETIM 6.0	EC002585
ETIM 7.0	EC002585
ETIM 8.0	EC002585
UNSPSC 16.0901	31163032

Dimensional drawing



Dimensions in mm (inch)

Connection diagram



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com