

# ES21-SB14G1

ES21

**SAFETY COMMAND DEVICES** 





## Ordering information

Туре	Part no.
ES21-SB14G1	6053944

Product consists of UL certified components (ES21-XC050, ES21-CS0001, ES21-CS0100, ES21-CS1000, ES21-AT1120). See UL certificate number: E198242

Other models and accessories → www.sick.com/ES21



#### Detailed technical data

#### **Features**

Number of positive action N/C contacts	2
Number of N/O contacts	1
Actuation directions	1
Contact module for panel mount version	✓
Obstruction protection	✓
Release type	Rotary release
Labeling "EMERGENCY STOP"	✓

#### Safety-related parameters

#### **Functions**

Safe series connection	None, only individual wiring (with diagnostics)
------------------------	---

#### Interfaces

Connection type	Terminal strip
Conductor cross section	≤ 2.5 mm²
Contact	Screw connection

#### Electrical data

#### Operating data

Protection class	II (EN 50178)
Switching principle	Slow action switching element
Number of positive action N/C contacts	2
Number of N/O contacts	1
Usage category	AC-15/DC-13 (EN 60947-5-1)
Rated operating current (voltage)	3 A (250 V AC) 2 A (24 V DC)
Rated insulation voltage U <sub>i</sub>	600 V
Switching voltage	≥ 5 V DC


Switching current	≥ 1 mA
Mechanical data	
Weight	150 g
Housing material	Plastic
Mounting version	Panel mount version
Ambient data	
Enclosure rating	IP65 (IEC 60529)
Ambient operating temperature	-30 °C +70 °C
Storage temperature	-50 °C +85 °C
Classifications	
eCl@ss 5.0	27371228
eCl@ss 5.1.4	27371228
eCl@ss 6.0	27371244
eCl@ss 6.2	27371244
eCl@ss 7.0	27371244
eCl@ss 8.0	27371244
eCl@ss 8.1	27371244
eCl@ss 9.0	27371244
eCl@ss 10.0	27371244
eCl@ss 11.0	27371244
eCl@ss 12.0	27371244
ETIM 5.0	EC002034
ETIM 6.0	EC002034
ETIM 7.0	EC002034
ETIM 8.0	EC002034

39121545


## Dimensional drawing (Dimensions in mm (inch))


#### Mounting holes


UNSPSC 16.0901



#### Panel mount version







# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

