



# GPS antenna

GPS antennas

ANTENNAS

**SICK**  
Sensor Intelligence.



Ordering information

Type	part no.
GPS antenna	6067023

Other models and accessories → [www.sick.com/GPS\\_antennas](http://www.sick.com/GPS_antennas)

Detailed technical data

Features

Accessory group	GPS antennas
Description	Compact, energy-efficient and water-resistant GPS antenna with variable pretension, high amplification and low noise
Frequency band	1575.42 ± 2 MHz
Polarization	R.H.C.P.
Ambient operating temperature	-40 °C ... +80 °C
Dimensions (W x H x L)	44 mm x 14.5 mm x 35.4 mm

Classifications

ECLASS 5.0	27279290
ECLASS 5.1.4	27279290
ECLASS 6.0	27279290
ECLASS 6.2	27279290
ECLASS 7.0	27279290
ECLASS 8.0	27279290
ECLASS 8.1	27279290
ECLASS 9.0	27279090
ECLASS 10.0	27279090
ECLASS 11.0	27279090
ECLASS 12.0	27279090
ETIM 5.0	EC001195
ETIM 6.0	EC001195
ETIM 7.0	EC001195
ETIM 8.0	EC001195
UNSPSC 16.0901	45121622

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)