



SAPPBOD-07A0009

Safe Interlocking

SAFETY SYSTEMS FOR MOVEMENT MONITORING

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SAPPB0D-07A0009	1087156

Included in delivery: DFS60S-BDOC01024 (1), FX3-CPU000000 (1), FX3-MOC000000 (1), FX3-MPL000001 (1), FX3-XTDI800002 (1), FX3-XTIO84002 (2), RE23-SA64 (1), TR10-SRU01C (1)

Other models and accessories → www.sick.com/Safe_Interlocking

Detailed technical data

Features

Safety task	Access protection
Application	Movement monitoring
Items supplied	1 DFS60S Pro safety encoder 1 RE2 safety switch 1 TR10 Lock safety locking device 1 Flexi Soft main module FX3-CPU0 1 Flexi Soft system plug FX3-MPL0 1 Flexi Soft I/O module FX3-XTIO 1 Flexi Soft I/O module FX3-XTDI 1 Flexi Soft motion control module FX3-MOCO

Mechanical data - Encoder

Mechanical design	Blind hollow shaft with feather key groove
Shaft diameter	10 mm

Classifications

ECLASS 5.0	27279090
ECLASS 5.1.4	27279090
ECLASS 6.0	27279090
ECLASS 6.2	27279090
ECLASS 7.0	27279090
ECLASS 8.0	27279090
ECLASS 8.1	27279090
ECLASS 9.0	27279090
ECLASS 10.0	27279090
ECLASS 11.0	27279090
ECLASS 12.0	27279090
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705

Recommended accessories

Other models and accessories → www.sick.com/Safe_Interlocking

	Brief description	Type	part no.
connectors and cables			
	Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 15 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals, Uncontaminated zones	YF2A14-150VB3XLEAX	2096237
	Connection type head A: Female connector, M12, 8-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 20 m, 8-wire, PUR, halogen-free Description: Sensor/actuator cable, unshielded Application: Uncontaminated zones, Zones with oils and lubricants, Robot, Drag chain operation	YF2A18-200UA5XLEAX	2095680
	Connection type head A: Male connector, Micro D-Sub, 15-pin, angled Connection type head B: Female connector, M12, 8-pin, straight, A-coded Cable: 5 m Description: Shielded	Connection cable	2094427

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com