

1

Choose your replacement product.

2

Choose the type of light

3

Choose the required replacement accessories.

1.



L27

Housing:	ABS (plastic)
Scanning range [m]:	0 ... 25 m
System connection:	M12, 4-pin, straight
Type of light:	Visible red light
Front screen heating:	yes

Transmitter		Receiver	
Type	Part number	Type	Part number
L27S-3D2430	2043906	L27E-3P2430	2043904

Housing:	ABS (plastic)
Scanning range [m]:	0 ... 25 m
System connection:	M12, 4-pin, straight
Type of light:	Visible red light
Front screen heating:	no

Transmitter		Receiver	
Type	Part number	Type	Part number
L27S-3D2450	2043877	L27E-3P2450	2043876

Housing:	ABS (plastic)
Scanning range [m]:	0 ... 25 m
System connection:	Q7, 7-pin, straight
Type of light:	Visible red light
Front screen heating:	no

Transmitter		Receiver	
Type	Part number	Type	Part number
L27S-3D3730	2043859	L27E-3P3730	2043858

2.



L26

no successor for heating, convert to standard version

Housing:	VISTAL® (plastic)
Scanning range [m]:	0 ... 50 m
System connection:	M12, 4-pin, (270° degree turnable)
Type of light:	Visible red light

Transmitter		Receiver	
Type	Part number	Type	Part number
WSO26P-243ZZ1A0ZZZZLLZZZZZZZ1	2113106	WEO26P-2416R500A00ZLLZZZZZZZ1	2113109

Housing:	VISTAL® (plastic)
Scanning range [m]:	0 ... 50 m
System connection:	M12, 4-pin, (270° degree turnable)
Type of light:	Infrared light

Transmitter		Receiver	
Type	Part number	Type	Part number
WSO26I-243ZZ1A0ZZZZLLZZZZZZZ1	2113107	WEO26I-2416R500A00ZLLZZZZZZZ1	2113110

no successor, convert to M12 version

3.

Replacement



No replacement accessories necessary

L28



Housing:	ABS (plastic)
Scanning range [m]:	0 ... 12 m
System connection:	M12, 4-pin, straight
Type of light:	Visible red light
Front screen heating:	no

Transmitter		Receiver	
Type	Part number	Type	Part number
L28S-3D2431	2044515	L28E-3P2431	2044516



L25

Housing:	VISTAL® (plastic)
Scanning range [m]:	0 ... 20 m
System connection:	M12, 4-pin, (270° degree turnable)
Type of light:	Visible red light

Transmitter		Receiver	
Type	Part number	Type	Part number
WSO16P-243ZZ1A0ZZZZLLZZZZZZZ1	2113101	WEO16P-2416R500A00ZLLZZZZZZZ1	2113102

Housing:	VISTAL® (plastic)
Scanning range [m]:	0 ... 20 m
System connection:	M12, 4-pin, (270° degree turnable)
Type of light:	Infrared light

Transmitter		Receiver	
Type	Part number	Type	Part number
WSO16I-243ZZ1A0ZZZZLLZZZZZZZ1	2113103	WEO16I-2416R500A00ZLLZZZZZZZ1	2113105

Replacement



Mechanical Replacement
Easy-to-install adapter: **2095677**