



## Display modules

**SICK**  
Sensor Intelligence.



## Product description

Display modules from SICK offer clear and easy-to-read displays for monitoring and controlling processes thus enabling simple operation and fast error diagnosis.

## Ordering information

Other models and accessories → [www.sick.com/Display\\_modules](http://www.sick.com/Display_modules)

Description	Type	Part no.
Digital display with resistive touch screen, for SPEETEC, incremental encoders and measuring wheel encoders. Multi-function device for use as tachometer, speed measuring device, pulse counter, position display, piece counter and total counter. Communication interface: incremental. Communication interface detailed: RS-422, RS485	DIS-IPDTACCR0000	4119630
Evaluation unit: OD Precision, 5 x NPN	AOD5-N1	6035984
Evaluation unit: OD Precision, 5 x PNP	AOD5-P1	6035985
OD Max evaluation unit, 5x NPN, required for OD25-01T1	AODG-N1	6030979
OD Max evaluation unit, 5x NPN, required for OD350-x, OD85-x and OD30-x	AOD-N1	6028961
OD Max evaluation unit, 5x PNP, required for OD25-01T1	AODG-P1	6030978
OD Mini evaluation unit, OD5000 and OL1, master, 3 x Q, 1 x analog, open end cable, 2 m	AOD1-MR27C4	6058195
OD Mini evaluation unit, OD5000 and OL1, slave, 3 x Q, 1 x analog, open end cable, 2 m	AOD1-SR27C4	6058196
OD Mini evaluation unit, master, 2 x Q, 2 x analog, 1 x IN; open end cable, 2 m	AOD1-MR27D4	6070574
OD Mini evaluation unit, master, 2 x Q, M12 male connector, 5-pin	AOD1-MR25Q2	6054272
OD Mini evaluation unit, slave, 1 x Q, M8 male connector, 4-pin	AOD1-SR24Q1	6054271
OD Mini evaluation unit, slave, 2 x Q, M12 male connector, 5-pin	AOD1-SR25Q2	6054273
Operator panel for the Inspector VSP product family, except VSPI-4xxxx. The operator panel supports the display of images and results, switching between recipes, and the management of Inspector configurations. The Inspector Viewer has a 100 Mbit/s Ethernet interface and requires a 24 V DC voltage supply.	SIU2-L0011A002	2084701
Table housing suitable for installation of the DIS-IPDTACCR0000 display unit	DIS-DH30M	7135599
Visualization of read results and read diagnosis data	CMD400	2029466

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)