





## SX0B-B1505G

System plugs S300

SYSTEM PLUGS AND EXTENSION MODULES

**SICK**  
Sensor Intelligence.



### Ordering information

| Type        | part no. |
|-------------|----------|
| SX0B-B1505G | 2034264  |

Other models and accessories → [www.sick.com/System\\_plugs\\_S300](http://www.sick.com/System_plugs_S300)

Illustration may differ



### Detailed technical data

#### Features

|                        |                                                                                      |
|------------------------|--------------------------------------------------------------------------------------|
| <b>Connection type</b> | Flying leads                                                                         |
| <b>Cable</b>           | 5 m, 15-wire, PVC                                                                    |
| <b>Jacket material</b> | PVC                                                                                  |
| <b>Shielding</b>       | Unshielded                                                                           |
| <b>Special feature</b> | Pre-assembled, Not for use of incremental encoders, integrated configuration storage |
| <b>Items supplied</b>  | With 1 x cable gland M16, 1 x blanking plug M16, 2 x blanking plug M12               |
| <b>Description</b>     | For S300 Advanced, Expert and Professional                                           |

#### Certificates

|                                     |   |
|-------------------------------------|---|
| <b>EU declaration of conformity</b> | ✓ |
| <b>UK declaration of conformity</b> | ✓ |
| <b>China RoHS</b>                   | ✓ |
| <b>EC-Type-Examination approval</b> | ✓ |
| <b>China GB certificate</b>         | ✓ |

#### Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27272790 |
| <b>ECLASS 5.1.4</b> | 27272790 |
| <b>ECLASS 6.0</b>   | 27272790 |
| <b>ECLASS 6.2</b>   | 27272790 |
| <b>ECLASS 7.0</b>   | 27272790 |
| <b>ECLASS 8.0</b>   | 27272790 |
| <b>ECLASS 8.1</b>   | 27272790 |
| <b>ECLASS 9.0</b>   | 27272792 |
| <b>ECLASS 10.0</b>  | 27272792 |
| <b>ECLASS 11.0</b>  | 27272792 |
| <b>ECLASS 12.0</b>  | 27272792 |
| <b>ETIM 5.0</b>     | EC011349 |

|                |          |
|----------------|----------|
| ETIM 6.0       | EC011349 |
| ETIM 7.0       | EC011349 |
| ETIM 8.0       | EC011349 |
| UNSPSC 16.0901 | 39121421 |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)