



Weather protection cover 270°

Protective caps and hoods

DEVICE PROTECTION AND CARE

SICK
Sensor Intelligence.

Weather protection cover 270° | Protective caps and hoods

DEVICE PROTECTION AND CARE



Ordering information

Type	part no.
Weather protection cover 270°	2046458

Other models and accessories → www.sick.com/Protective_caps_and_hoods

Detailed technical data


Features

Product segment	Device protection and care
Product	Protective caps and hoods
Description	Weather protection hood 270°
Suitable for	LMS10x, LMS11x, LMS12x, LMS13x, LMS14x, LMS15x, S100
Items supplied	Weather hood, 270°, 3 x M5 x 12 screws
Material	Cast aluminum (3.2581.02), ALMG3G22 (3.3535.24)
Weight	1.88 kg

Classifications

ECLASS 5.0	27371205
ECLASS 5.1.4	27371205
ECLASS 6.0	27371205
ECLASS 6.2	27371205
ECLASS 7.0	27371205
ECLASS 8.0	27371205
ECLASS 8.1	27371205
ECLASS 9.0	27371205
ECLASS 10.0	27371205
ECLASS 11.0	27371205
ECLASS 12.0	27371205
ETIM 5.0	EC000200
ETIM 6.0	EC000200
ETIM 7.0	EC000200
ETIM 8.0	EC000200
UNSPSC 16.0901	32131023


Dimensional drawing Weather hood, 270°



Dimensions in mm (inch)

- ① If the sensor is mounted upside down, the label on top of the weather protection hood must be removed.
- ② Mounting kit for weather protection hood (2046025)
- ③ Quick clamp (2046989)

Dimensional drawing Weather hood, 270°



Dimensions in mm (inch)

- ① If the sensor is mounted upside down, the label on top of the weather protection hood must be removed.
- ② Mounting kit for weather protection hood (2046025)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com