



Connection cable

Other connectors and cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
Connection cable	2067799

Other models and accessories → www.sick.com/Other_connectors_and_cables



Detailed technical data

Technical specifications

Connection type head A	Male connector, Micro D-Sub, 15-pin, straight
Connection type head B	Male connector, D-Sub-HD, 15-pin, straight
Cable	10 m
Shielding	Shielded
Note	For connecting the Motion Control Module FX3-MOC with a motor feedback splitter box or a dual encoder connector box


Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304
ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604


Dimensional drawing



Dimensions in mm (inch)


Part number	L1 [mm]	L1 [inch]
2067798	2000 +100	78.74 +3.94
2067799	10000 +500	393.70 +19.69
2126044	2000 +100	78.74 +3.94

PIN assignment



Male connector, Micro D-Sub, 15-pin			Male connector, D-Sub, 15-pin	
FX3-MOC			FX3-EBX connection unit	
Pin	Designation		Pin	
1	ENC1_A+		1	
2	ENC1_B+		6	
3	ENC1_C+		11	
4	ENC1_24V		3	
5	ENC2_24V		13	
6	ENC2_C+		14	
7	ENC2_B+		9	
8	ENC2_A+		4	
9	ENC1_A-		2	
10	ENC1_B-		7	
11	ENC1_C-		12	
12	ENC_0V		8	
13	ENC2_C-		15	
14	ENC2_B-		10	
15	ENC2_A-		5	

PIN assignment



Male connector, Micro D-Sub, 15-pin			Male connector, D-Sub, 15-pin	
FX3-MOC			FX3-EBX connection unit	
Pin	Designation		Pin	
1	ENC1_A+		1	
2	ENC1_B+		6	
3	ENC1_C+		11	
4	ENC1_24V		3	
5	ENC2_24V		13	
6	ENC2_C+		14	
7	ENC2_B+		9	
8	ENC2_A+		4	
9	ENC1_A-		2	
10	ENC1_B-		7	
11	ENC1_C-		12	
12	ENC_OV		8	
13	ENC2_C-		15	
14	ENC2_B-		10	
15	ENC2_A-		5	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com