



## Connection cable

Other connectors and cables

**CONNECTORS AND CABLES**

**SICK**  
Sensor Intelligence.



## Ordering information

Type	part no.
Connection cable	2067801

Other models and accessories → [www.sick.com/Other\\_connectors\\_and\\_cables](http://www.sick.com/Other_connectors_and_cables)



## Detailed technical data

## Technical specifications

<b>Connection type head A</b>	Male connector, D-Sub-HD, 15-pin, straight
<b>Connection type head B</b>	Male connector, D-Sub, 9-pin, straight
<b>Cable</b>	10 m
<b>Shielding</b>	Shielded
<b>Note</b>	To connect two motor feedback splitter boxes


## Certificates

<b>EU declaration of conformity</b>	✓
<b>UK declaration of conformity</b>	✓

## Classifications

<b>ECLASS 5.0</b>	19030312
<b>ECLASS 5.1.4</b>	19030312
<b>ECLASS 6.0</b>	27060304
<b>ECLASS 6.2</b>	27060304
<b>ECLASS 7.0</b>	27060304
<b>ECLASS 8.0</b>	27060304
<b>ECLASS 8.1</b>	27060304
<b>ECLASS 9.0</b>	27060304
<b>ECLASS 10.0</b>	27060304
<b>ECLASS 11.0</b>	27060304
<b>ECLASS 12.0</b>	27060304
<b>ETIM 5.0</b>	EC000830
<b>ETIM 6.0</b>	EC000830
<b>ETIM 7.0</b>	EC003249
<b>ETIM 8.0</b>	EC003249
<b>UNSPSC 16.0901</b>	26121604


## Dimensional drawing



Dimensions in mm (inch)


Part number	L1 [mm]	L1 [inch]
2067800	300 +25	11.81 +0.98
2067801	2000 +100	78.74 +3.94
2078260	10000 +500	393.70 +19.69

## PIN assignment



Male connector, D-Sub, 9-pin		Male connector, D-Sub, 15-pin	
FX3-EBX3 connection unit		FX3-EBX3 or FX3-EBX4 connection unit	
Pin	Designation	Pin	Designation
1	ENC_A+	1	ENC_A+
2	ENC_B+	6	ENC_B+
3	ENC_C+	11	ENC_C+
4	Reserved	3	Reserved
5	ENC_24V	13	ENC_24V
6	ENC_A-	2	ENC_A-
7	ENC_B-	7	ENC_B-
8	ENC_C-	12	ENC_C-
9	ENC_OV	8	ENC_OV

## PIN assignment



Male connector, D-Sub, 9-pin		Male connector, D-Sub, 15-pin	
FX3-EBX3 connection unit		FX3-EBX3 or FX3-EBX4 connection unit	
Pin	Designation	Pin	Designation

Male connector, D-Sub, 9-pin		Male connector, D-Sub, 15-pin	
1	ENC_A+	1	ENC_A+
2	ENC_B+	6	ENC_B+
3	ENC_C+	11	ENC_C+
4	Reserved	3	Reserved
5	ENC_24V	13	ENC_24V
6	ENC_A-	2	ENC_A-
7	ENC_B-	7	ENC_B-
8	ENC_C-	12	ENC_C-
9	ENC_OV	8	ENC_OV

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is "Sensor Intelligence."**

## WORLDWIDE PRESENCE:

Contacts and other locations [www.sick.com](http://www.sick.com)