



DOL-0803-W02MN

Other connectors and cables

CONNECTORS AND CABLES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
DOL-0803-W02MN	6033667

Other models and accessories → www.sick.com/Other_connectors_and_cables

Detailed technical data

Technical specifications


Connection type head A	Female connector, M8, 3-pin, angled	
Connection type head B	Flying leads	
Connection type	Flying leads	
Connector material	PP	
Connector color	White	
Locking nut material	Stainless steel (V4A/1.4404/316L)	
Tightening torque	0.6 Nm	
Cable	2 m, 3-wire, PP	
Jacket material	PP	
Jacket color	Blue-gray	
Cable diameter	4.6 mm	
Conductor cross section	0.34 mm ²	
Shielding	Unshielded	
Bending radius	Flexible use	> 10 x cable diameter
		> 5 x cable diameter
Reference voltage	≤ 60 V	
Current loading	4 A	
Application	Hygienic and washdown zones Drag chain operation	
Enclosure rating	IP67/ IP69K	
Operating temperature	Flexible use	-40 °C ... +105 °C
		-40 °C ... +105 °C
		-40 °C ... +105 °C

Classifications

ECLASS 5.0	19030312
ECLASS 5.1.4	19030312
ECLASS 6.0	27060304
ECLASS 6.2	27060304

ECLASS 7.0	27060304
ECLASS 8.0	27060304
ECLASS 8.1	27060304
ECLASS 9.0	27060304
ECLASS 10.0	27060304
ECLASS 11.0	27060304
ECLASS 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

Dimensional drawing



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com