


UHF Transponder, rectangular, high-temp, global

UHF transponders

RFID TRANSPONDERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
UHF Transponder, rectangular, high-temp, global	6049636

Other models and accessories → www.sick.com/UHF_transponders

Detailed technical data

Features

Accessory group	UHF transponders
Description	UHF transponder, global, 110 mm x 70 mm x 0.42 mm, NXP UCODE G2XM
Specialty	High Temperature
Frequency band	UHF (860 MHz ... 960 MHz)
Carrier frequency	865 MHz ... 928 MHz
Read range	
	RFU61x 70 cm ¹⁾
	RFU62x 90 cm ¹⁾
	RFU63x/RFU65x 400 cm ¹⁾
Design	Rectangular
Housing material	Textile
Ambient operating temperature	-40 °C ... +85 °C
Storage temperature	-40 °C ... +85 °C
Housing color	Beige
IC type	NXP UCODE G2XM
IC capacity	96/240 Bit
IC data retention time	< 50 years
Mounting method	Plastic clip
Dimensions (W x H x L)	110 mm x 0.42 mm x 70 mm
Weight	+ 2.5 g

¹⁾ Typical value; actual value depends on environmental conditions.

Certificates

China RoHS	✓
-------------------	---

Classifications

ECLASS 5.0	27280401
ECLASS 5.1.4	27280401
ECLASS 6.0	27280401
ECLASS 6.2	27280401
ECLASS 7.0	27280401

ECLASS 8.0	27280401
ECLASS 8.1	27280402
ECLASS 9.0	27280402
ECLASS 10.0	27280402
ECLASS 11.0	27280402
ECLASS 12.0	27280402
ETIM 5.0	EC002593
ETIM 6.0	EC002998
ETIM 7.0	EC002998
ETIM 8.0	EC002998
UNSPSC 16.0901	52161523

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com