



# UHF Transponder, ISO-card, global

UHF transponders

RFID TRANSPONDERS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
UHF Transponder, ISO-card, global	6051820

Other models and accessories → [www.sick.com/UHF\\_transponders](http://www.sick.com/UHF_transponders)

### Detailed technical data

#### Features

<b>Accessory group</b>	UHF transponders
<b>Description</b>	UHF transponder, PVC, 85.6 mm x 54 mm x 0.76 mm, Alien Higgs
<b>Frequency band</b>	UHF (860 MHz ... 960 MHz)
<b>Carrier frequency</b>	865 MHz ... 928 MHz
<b>Read range</b>	
	RFU61x 60 cm <sup>1)</sup>
	RFU62x 100 cm <sup>1)</sup>
	RFU63x/RFU65x 400 cm <sup>1)</sup>
<b>Design</b>	Rectangular
<b>Housing material</b>	PVC
<b>Ambient operating temperature</b>	-10 °C ... +50 °C
<b>Storage temperature</b>	-10 °C ... +50 °C
<b>Housing color</b>	White
<b>IC type</b>	Impinj Monza 4QT
<b>IC capacity</b>	128/512 Bit
<b>IC data retention time</b>	< 50 years
<b>Mounting method</b>	Recessed
<b>Dimensions (W x H x L)</b>	85.6 mm x 0.76 mm x 53.98 mm
<b>Weight</b>	+ 6 g

<sup>1)</sup> Typical value; actual value depends on environmental conditions.

#### Classifications

<b>ECLASS 5.0</b>	27280401
<b>ECLASS 5.1.4</b>	27280401
<b>ECLASS 6.0</b>	27280401
<b>ECLASS 6.2</b>	27280401
<b>ECLASS 7.0</b>	27280401
<b>ECLASS 8.0</b>	27280401
<b>ECLASS 8.1</b>	27280402

<b>ECLASS 9.0</b>	27280402
<b>ECLASS 10.0</b>	27280402
<b>ECLASS 11.0</b>	27280402
<b>ECLASS 12.0</b>	27280402
<b>ETIM 5.0</b>	EC002593
<b>ETIM 6.0</b>	EC002998
<b>ETIM 7.0</b>	EC002998
<b>ETIM 8.0</b>	EC002998
<b>UNSPSC 16.0901</b>	52161523

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)