



SLB060-0B010K700

Acoustic signal transmitters

SIGNAL TRANSMITTERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
SLB060-0B010K700	6076072

Other models and accessories → www.sick.com/Acoustic_signal_transmitters



Detailed technical data

Features

Product segment	Signal transmitters
Product	Acoustic signal transmitters
Description	This product is a buzzer unit exclusively for model SLT060-0B010J700.
Power consumption	≤ 5 W

Certificates



EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
cULus certificate	✓

Classifications

ECLASS 5.0	27371237
ECLASS 5.1.4	27371237
ECLASS 6.0	27371237
ECLASS 6.2	27371237
ECLASS 7.0	27371237
ECLASS 8.0	27371237
ECLASS 8.1	27371237
ECLASS 9.0	27371237
ECLASS 10.0	27371237
ECLASS 11.0	27371237
ECLASS 12.0	27371237
ETIM 5.0	EC000232
ETIM 6.0	EC000232

ETIM 7.0	EC000232
ETIM 8.0	EC000232
UNSPSC 16.0901	39121107

Instruction for installation



- ① Head cover
- ② locked
- ③ unlocked
- ④ Smart Light Buzzer

Adjustments Adjustment

Buzzer Sound /Typical Frequency	No.1	No sound
	No.2	Continuous beep sound / 3378Hz
	No.3	Rapid intermittent beep / 3378Hz
	No.4	Rapid Hi-Lo / 2016Hz&3012Hz
	No.5	Sweep sound / 1000Hz-4032Hz
	No.6	Beep sound / 3378Hz 500ms ON / 500ms OFF
	No.7	Rapid intermittent beep / 3378Hz 500ms ON / 500ms OFF
	No.8	Rapid Hi-Lo / 2016Hz&3012Hz 500ms ON / 500ms OFF
	No.9	Sweep sound / 1000Hz-4032Hz 500ms ON / 500ms OFF

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com