




# MB1-BF10

MB1

**MECHANICAL BOLTS**

**SICK**  
Sensor Intelligence.



## Ordering information

| Type     | part no. |
|----------|----------|
| MB1-BF10 | 1111207  |

Other models and accessories → [www.sick.com/MB1](http://www.sick.com/MB1)

## Detailed technical data

### Features

|                                                       |                                                                                                                                             |
|-------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Description</b>                                    | Complete set consisting of door bolting unit with frame plate for flexLock and adapters for actuators                                       |
| <b>Installation tolerance (horizontal)</b>            | 3 mm ... 30 mm                                                                                                                              |
| <b>Model</b>                                          |                                                                                                                                             |
| Catch release button/ANSI-compliant locking mechanism | ✓                                                                                                                                           |
| Escape release                                        | –                                                                                                                                           |
| Frame plate with latching function                    | –                                                                                                                                           |
| <b>Suitable for</b>                                   | flexLock safety locking device (with actuator FXL-AR1)                                                                                      |
| <b>Items supplied</b>                                 | Frame plate flexLock<br>Adapter for actuator mounting (MB1-BRFL)<br>Safety screws for installing provided adapters<br>Mounting instructions |

### Mechanics


|                                           |                                 |
|-------------------------------------------|---------------------------------|
| <b>Weight</b>                             | 1.606 kg                        |
| <b>Material</b>                           |                                 |
| Handle                                    | VISTAL®                         |
| Bolt unit                                 | Steel, zinc coated              |
| Sliding carriage, base plate, frame plate | Aluminum (coated)<br>Polyketone |

### Classifications

|                     |          |
|---------------------|----------|
| <b>ECLASS 5.0</b>   | 27279202 |
| <b>ECLASS 5.1.4</b> | 27279202 |
| <b>ECLASS 6.0</b>   | 27279202 |
| <b>ECLASS 6.2</b>   | 27279202 |
| <b>ECLASS 7.0</b>   | 27279202 |
| <b>ECLASS 8.0</b>   | 27279202 |
| <b>ECLASS 8.1</b>   | 27279202 |
| <b>ECLASS 9.0</b>   | 27273701 |

|                       |          |
|-----------------------|----------|
| <b>ECLASS 10.0</b>    | 27273701 |
| <b>ECLASS 11.0</b>    | 27273701 |
| <b>ETIM 5.0</b>       | EC002594 |
| <b>ETIM 6.0</b>       | EC002594 |
| <b>ETIM 7.0</b>       | EC002594 |
| <b>ETIM 8.0</b>       | EC002594 |
| <b>UNSPSC 16.0901</b> | 31161606 |

## Dimensional drawing



Dimensions in mm (inch)

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

**For us, that is “Sensor Intelligence.”**

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)