



ICL260-F222-Set01-(red)

Illuminations

REFLECTORS AND OPTICS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
ICL260-F222-Set01-(red)	1053193

Included in delivery: ICL260-F222 (1), Mounting bracket (1), Connecting cable for ICL illumination (1)

Other models and accessories → www.sick.com/illuminations

Detailed technical data

Features


Product segment	Reflectors and optics
Product	Illuminations
Product version	LED
Description	Ring illumination set ICL260-F222, bright field for ICR84x-2L, red illumination, distance 200 mm to 1.5 m incl. mounting bracket, screws and connection cable (2 m) for ring illumination
LED class	Risk group 1 (low risk, IEC62471 : 2006)
Power consumption	≤ 5 W
Ambient operating temperature	0 °C ... +40 °C ¹⁾
Storage temperature	-25 °C ... +70 °C ¹⁾

¹⁾ Relative humidity: 93 %.

Classifications

ECLASS 5.0	27110635
ECLASS 5.1.4	27110635
ECLASS 6.0	27110635
ECLASS 6.2	27110635
ECLASS 7.0	27110635
ECLASS 8.0	27110635
ECLASS 8.1	27110635
ECLASS 9.0	27110635
ECLASS 10.0	27110635
ECLASS 11.0	27110635
ECLASS 12.0	27110635
ETIM 5.0	EC000996
ETIM 6.0	EC000996
ETIM 7.0	EC000996
ETIM 8.0	EC000996
UNSPSC 16.0901	39101628

Reading field diagram



- Illuminated field ICL170-F222
- Illuminated field ICL260-F222
- Illuminated field ICL280-F222, ICL280-F202S01
- Illuminated field ICL300-F222, ICL300-F202S01

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com