



MZ2Q-T

Cylinder sensors with two individually adjustable switching points
for T-slot cylinders

SICK
Sensor Intelligence.



Technical data overview

Output function	2 x N/O contact / 2 x N/O contact / IO-Link (depends on variant)
IO-Link	- / ✓ (depends on variant)
Teach-in	Yes
Cylinder types with adapter	Profile cylinder Tie rod cylinder Round body cylinder Dovetail groove cylinder SMC rail CDQ2 SMC rail ECDQ2
Housing length	40 mm

Product description

On pneumatic cylinders, grippers, or carriages, the MZ2Q-T cylinder sensors from SICK are able to detect two end positions or intermediate positions with just one sensor. This is achieved by using two individually adjustable switching points in one sensor housing. This is much easier, quicker, and more cost-effective than conventional solutions, since only one slot is used. As a result, mounting and cabling overheads are halved and applications can be solved efficiently.

At a glance

- Can be used in all standard cylinders, linear slides, and grippers using the T-slot and – with the help of adapters – in round rod, tie-rod, and profile cylinders, and cylinders with a dovetail groove
- Drop-in mounting from above simplifies handling and assembly
- Easy adjustment of two switching points via teach-in pushbutton
- LEDs for indicating the two switching points
- Detection range up to 50 mm stroke

Your benefits

- One sensor, two switching points: Reduces commissioning time and costs
- Maximum flexibility thanks to a detection zone up to 50 mm
- Suitable for precise pneumatic applications due to intuitive and precise definition of two switching points
- Quick and easy installation and sensor replacement thanks to drop-in sensor mounting
- Flexible sensor settings, monitoring, advanced diagnostics and visualization through IO-Link (depending on type)

Fields of application

- End position detection in pneumatic miniature cylinders
- Position detection (open/close) in pneumatic grippers

Ordering information

Other models and accessories → www.sick.com/MZ2Q-T

- **Electrical wiring:** DC 4-wire

Connection type	Output function	Smart Sensor	Communication interface	Type	Part no.
Cable with M8 male connector, 4-pin, 0.3 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KP0	1029846
				MZ2Q-FTZPS-KPOS03	1051024
Cable with connector M12, 4-pin, with knurled nut, 0.3 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KQ0	1041323
	2 x N/O contact, IO-Link	Enhanced Sensing, efficient communication	IO-Link	MZ2Q-TSLPSKQ0	1042228
Cable with connector M12, 4-pin, with knurled nut, 0.8 m	2 x N/O contact	-	-	MZ2Q-TFSPSKQD	1062172
Cable with connector M8, 4-pin, with knurled nut, 0.3 m	2 x N/O contact, IO-Link	Enhanced Sensing, efficient communication	IO-Link	MZ2Q-TSLPSKR0	1146366
Cable with connector M8, 4-pin, with knurled nut, 0.5 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KR0	1041322
Cable with plug, M8, 4-pin, angled, with knurled nut, with PTFE hose, 0.25 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KRDS27	1152305
Cable, 4-wire, stripped, 0.02 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KUDS24	1132823
Cable, 4-wire, stripped, 2 m	2 x N/O contact	-	-	MZ2Q-FTZNS-KU0	1048103
	2 x N/O contact, IO-Link	Enhanced Sensing, efficient communication	IO-Link	MZ2Q-TSLPSKU0	1115197
Cable, 4-wire, stripped, 5 m	2 x N/O contact	-	-	MZ2Q-FTZPS-KUB	1045267

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com