



IMM

Inductive miniature sensors for industrial use

SICK
Sensor Intelligence.


Advantages




Maximum sensing ranges for great freedom in machine design

Minimal space requirements thanks to the tiny dimensions are what characterize the IMM miniature sensors from SICK. And they make no compromises when it comes to performance. With their large sensing ranges of up to 6 mm, they IMM ensure stable processes and detect objects from a safe distance. The combination of a large sensing range and minimal space requirements increases freedom for machine design as well as the field of application of the sensors. This means not only can non-ferrous metals be detected at long distances, but the sensors can also be used where currently only larger sensors are deployed due to the required sensing ranges.

Perfectly suited for applications with tight installation space but high standards on the sensing range.



Thanks to the threefold sensing ranges of up to 6 mm, the IMM sensors detect every object from a safe distance.



The smallest IMM sensors are only 12 mm long and have a diameter of just 3 mm: This is how IMM sensors can fit in such small installation spaces.



Minimum space requirements of the sensors in the M8 and M12 sizes without compromises in the sensing range.



Stable processes and high flexibility in machine design thanks to large sensing ranges and compact miniature design



Fast, easy and safe installation

With IMM sensors, you save valuable time when installing the sensors, thereby increasing your productivity. Thanks to the visual adjustment indicator, you have a simple way to ensure reliable sensor function during operation. The high tightening torques and the specially-designed mounting accessories facilitate sensor mounting and ensure permanent and secure assembly. In addition, the IMM are equipped with IO-Link version 1.1. In addition to simple sensor diagnostics and easy access to data, this also supports the assembly process. Device exchange and identification therefore only takes a few seconds, and considerably less wiring work is required thanks to integration into the PLC system via remote IO-Link master modules.

Huge time savings during installation thanks to additional functions and accessories



Visual adjustment indicator: the LED signalizes when the secured sensing range has been reached.




Reinforced V2A housing for high tightening torques as well as associated mounting accessories make mounting even easier and more secure.



IO-Link: simple device exchange and quick device identification, minimal wiring effort and easy sensor diagnostics as well as easy access to data.



Thanks to the visual adjustment indicator, IO-Link as well as the associated accessories, installation of IMM sensors is quick and easy.



The best choice for highly dynamic handling and assembly processes

In addition to the compact size, the high positioning accuracy and precise switching behavior are the most significant requirements in handling and assembly processes. The IMM sensors with high switching frequency, high repeatability and stable switching signals fulfill these requirements unconditionally. While large sensors often reach their limits with very small objects, IMM devices reliably detect even small objects and are therefore optimally suited for the detection of the tiniest components in supply processes. The low weight of the sensors enables fast acceleration of moving components. A flexible cable is also available on request, which means that highly dynamic processes with several movement cycles per day are no longer a challenge.



High positioning accuracy and precise switching behavior for reliable detection of fast processes.



High detection sensitivity makes possible the detection of small objects such as wires, nuts and screws.



The low weight and flexible cables enable fast acceleration and high bending stresses in dynamic handling processes (flexible cable available on request).



IMM sensors are perfectly designed for handling and assembly applications



Technical data overview

Housing	Cylindrical / Metric (depends on variant)
Thread size	M4 x 0.5 M5 x 0.5
Diameter	Ø 3 mm ... Ø 6.5 mm (depends on variant)
Sensing range S_n	0.6 mm ... 6 mm (depends on variant)
Housing material	Stainless steel V2A
Enclosure rating	IP68 / IP69K / IP67 (depends on variant)
Housing	Cylindrical / Metric (depends on variant)
Thread size	M4 x 0.5 M5 x 0.5
Housing diameter	Ø 3 mm ... Ø 6.5 mm (depends on variant)
Sensing range S_n	0.6 mm ... 6 mm (depends on variant)
Electrical wiring	DC 3-wire
Housing material	Stainless steel V2A
Enclosure rating	IP68 / IP69K / IP67 (depends on variant)

Product description

Minimal space requirements paired with maximum performance characterize the IMM inductive proximity sensors. They allow the highest level of miniaturization without compromise. Thanks to the 3-fold sensing range up to 6 mm, IMM devices detect objects from a greater distance than before. Due to their small size, low weight and quick and precise switching behavior, the IMM sensors are ideal for highly dynamic handling and assembly processes. State-of-the-art ASIC technology enables the integration of a visual adjustment indicator as well as communication via IO-Link, version 1.1. This saves time for commissioning, reduces installation errors and turns the sensors into suppliers of data for future automation applications at the same time.

At a glance

- Design: M4 to M5, diameter: 3 mm to 6.5 mm
- Extended sensing ranges: 0.6 mm to 6 mm
- Electrical configuration: DC, 3-wire
- Enclosure rating: IP67
- Temperature range: -25 °C to +70 °C
- Rugged stainless-steel housing, plastic sensing face
- 3-fold sensing ranges, visual adjustment indicator, IO-Link communication

Your benefits

- Space-saving installation and significant flexibility in machine design thanks to the compact size
- High positioning accuracy and precise switching behavior for reliable detection of fast handling and assembly processes
- Stable processes and high plant availability thanks to 3-fold sensing range
- High detection sensitivity makes possible reliable detection of small objects
- High degree of flexibility and communication options thanks to IO-Link
- Simple mounting thanks to visual adjustment indicator
- The low weight of the sensor enables fast acceleration in dynamic handling processes

Fields of application

- Handling, assembly processes: positioning
- Supply processes: detecting tiny components, counting
- Small waves: speed monitoring, direction of movement detection
- Gripper: position detection (grripper open or closed)
- Linear or rotating gripper: positioning
- CNC workpiece changer and spindles: position detection

Ordering information

Other models and accessories → www.sick.com/IMM

- **Product version:** IH03
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire

Sensing range S _n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.6 mm	Standard design	NPN	NO	Cable, 3-wire, 2 m	IH03-0B6NS-VU1	6020142
		PNP	NC	Cable, 3-wire, 2 m	IH03-0B6PO-VU1	6020143
			NO	Cable with plug M8, 3-pin, with knurled nut, 0.2 m	IH03-0B6PS-VR1	6038602
				Cable, 3-wire, 2 m	IH03-0B6PS-VU1	6020141
				Cable, 3-wire, 5 m	IH03-0B6PS-VUB	6020630
0.8 mm	Short-body	NPN	NO	Cable, 3-wire, 2 m ¹⁾	IHP03-0B8NSVU2K	6058032
		PNP	NO	Cable, 3-wire, 2 m ¹⁾	IHP03-0B8PSVU2K	6058033
1 mm	Short-body	NPN	NO	Cable with connector M8, 3-pin, 0.2 m ¹⁾	IH03-01BNSVR8K	6058026
				Cable, 3-wire, 2 m ¹⁾	IH03-01BNSVU2K	6058024
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m ¹⁾	IH03-01BPSVR8K	6058027
				Cable, 3-wire, 2 m ¹⁾	IH03-01BPSVU2K	6058025

¹⁾ Do not bend below 0 °C.

- **Product version:** IM04
- **Cylindrical thread design:** M4
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire

Sensing range S_n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.6 mm	Standard design	NPN	NO	Cable, 3-wire, 2 m ¹⁾	IM04-0B6NS-ZU1	6020146
		PNP	NC	Cable, 3-wire, 2 m ¹⁾	IM04-0B6PO-ZU1	6020147
			NO	Cable with plug M8, 3-pin, with knurled nut, 0.2 m ¹⁾	IM04-0B6PS-ZR1	6042085
				Cable, 3-wire, 2 m ¹⁾	IM04-0B6PS-ZU1	6020145
				Cable, 3-wire, 5 m ¹⁾	IM04-0B6PS-ZUB	6020610
1 mm	Short-body	NPN	NO	Cable with connector M8, 3-pin, 0.2 m ¹⁾	IM04-01BNSVR8K	6058030
				Cable, 3-wire, 2 m ¹⁾	IM04-01BNSVU2K	6058028
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m ¹⁾	IM04-01BPSVR8K	6058031
				Cable, 3-wire, 2 m ¹⁾	IM04-01BPSVU2K	6058029

¹⁾ Do not bend below 0 °C.

- **Product version:** IH04
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 0.8 mm
- **Housing:** Standard design
- **Output function:** NO

Switching output	Connection type	Type	Part no.
NPN	Cable, 3-wire, 2 m	IH04-0B8NS-VW1	6020149
	Connector M8, 3-pin	IH04-0B8NS-VT1	6020152
PNP	Cable with connector M8, 3-pin, 0.2 m	IH04-0B8PS-VR1	6045178
	Cable, 3-wire, 2 m	IH04-0B8PS-VW1	6020113
	Cable, 3-wire, 85 mm	IH04-0B8PS-VUD	6054677
	Connector M8, 3-pin	IH04-0B8PS-VT1	6020114

- **Product version:** IM05
- **Cylindrical thread design:** M5
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Housing:** Standard design

Sensing range S_n	Switching output	Output function	Special features	Connection type	Type	Part no.
0.8 mm	NPN	NC	–	Cable, 3-wire, 2 m	IM05-0B8NO-ZW1	6020157
		NO	–	Cable, 3-wire, 2 m	IM05-0B8NS-ZW1	6020155
				Connector M8, 3-pin	IM05-0B8NS-ZT1	6020158
				Cable, 3-wire, 2 m	IM05-0B8NSVS2SS01	6066461
	PNP	NC	–	Connector M8, 3-pin	IM05-0B8PO-ZT1	6020159
		NO	–	Cable, 3-wire, 2 m	IM05-0B8PS-ZW1	6011591
				Cable, 3-wire, 5 m	IM05-0B8PS-ZWB	6021575
				Connector M8, 3-pin	IM05-0B8PS-ZT1	6020110
	1.5 mm	NPN	–	Cable, 3-wire, 2 m	IM05-1B5NOVU2S	6049734
				Connector M8, 3-pin	IM05-1B5NOVT0S	6049738
		NO	–	Cable, 3-wire, 2 m	IM05-1B5NSVU2S	6049733
				Connector M8, 3-pin	IM05-1B5NSVT0S	6049737
		PNP	–	Cable, 3-wire, 2 m	IM05-1B5POVU2S	6049736
				Connector M8, 3-pin	IM05-1B5POVT0S	6049740
		NO	–	Cable with plug M8, 3-pin, with knurled nut, 0.2 m	IM05-1B5PSVR8S	6069347
				Cable with plug M8, 3-pin, with knurled nut, 0.3 m	IM05-1B5PSVR9S	6069466
				Cable, 3-wire, 2 m	IM05-1B5PSVU2S	6049735
				Connector M8, 3-pin	IM05-1B5PSVT0S	6049739

- **Product version:** IH06
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire

Sensing range S _n	Housing	Switch- ing output	Output function	Connection type	Type	Part no.
1.5 mm	Extremely short model	NPN	NO	Cable, 3-wire, 2 m	IH06-1B5NS-VWK	6020166
				Connector M8, 3-pin	IH06-1B5NS-VTK	6020170
		PNP	NC	Cable, 3-wire, 2 m	IH06-1B5PO-VWK	6020167
				Connector M8, 3-pin	IH06-1B5PO-VTK	6020171
			NO	Cable, 3-wire, 2 m	IH06-1B5PS-VWK	6020165
					IH06-1B5PS-VWXS01	6033574
				Connector M8, 3-pin	IH06-1B5PS-VTK	6020169
				2 mm	Standard design	PNP

- **Product version:** IH06
- **Installation type:** quasi-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 2 mm

Housing	Switching output	Output function	Connection type	Type	Part no.
Standard design	NPN	NO	Cable, 3-wire, 2 m	IH06-02BNS-VW1	7900178
			Connector M8, 3-pin	IH06-02BNS-VT1	7900180
	PNP	NC	Connector M8, 3-pin	IH06-02BPO-VT1	1016857
			Cable, 3-wire, 2 m	IH06-02BPS-VW1	7900177
		NO	Connector M8, 3-pin	IH06-02BPS-VT1	7900179
			Cable, 3-wire, 2 m	IH06-02BPS-VW1	7900177
Short-body	NPN	NO	Cable, 3-wire, 2 m	IH06-02BNS-VWK	6025875
			Connector M8, 3-pin	IH06-02BNS-VTK	6025878
	PNP	NC	Connector M8, 3-pin	IH06-02BPO-VTK	6025879
			Cable, 3-wire, 2 m	IH06-02BPS-VWK	6025874
		NO	Cable, 3-wire, 2 m	IH06-02BPS-VW1	7900177
			Connector M8, 3-pin	IH06-02BPS-VTK	6025877

- **Product version:** IH06
- **Installation type:** non-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 4 mm

Housing	Switching output	Output function	Connection type	Type	Part no.
Standard design	NPN	NO	Cable, 3-wire, 2 m	IH06-04NNS-VW1	7900182
	PNP	NO	Cable, 3-wire, 2 m	IH06-04NPS-VW1	7900181
			Connector M8, 3-pin	IH06-04NPS-VT1	7900183

Housing	Switching output	Output function	Connection type	Type	Part no.
Short-body	NPN	NO	Cable, 3-wire, 2 m	IH06-04NNS-VWK	6025881
			Connector M8, 3-pin	IH06-04NNS-VTK	6025883
	PNP	NC	Connector M8, 3-pin	IH06-04NPO-VTK	6025884
		NO	Cable, 3-wire, 2 m	IH06-04NPS-VWK	6025880
			Connector M8, 3-pin	IH06-04NPS-VTK	6025882

- **Product version:** IHM03
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Special features:** Visual adjustment indicator

Sensing range S _n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.6 mm	Standard design	NPN	NC	Cable, 3-wire, 2 m	IHM03-0B6NOVU2S	1114508
			NO	Cable, 3-wire, 2 m	IHM03-0B6NSVU2S	1103991
		PNP	NC	Cable, 3-wire, 2 m	IHM03-0B6POVU2S	1111250
			NO	Cable with connector M8, 3-pin, 0.2 m	IHM03-0B6PSVR8S	1108736
				Cable, 3-wire, 2 m	IHM03-0B6PSVU2S	1102476
1 mm	Standard design	PNP	NC	Cable with connector M8, 3-pin, 0.2 m	IHM03-01BPOVR8S	1144067
				Cable, 3-wire, 2 m	IHM03-01BPOVU2S	1111251
		NO	NO	Cable with connector M8, 3-pin, 0.2 m	IHM03-01BPSVR8S	1108737
				Cable, 3-wire, 2 m	IHM03-01BPSVU2S	1097305
				Cable, 3-wire, 5 m	IHM03-01BPSVU5S	1153862
	Short-body	NPN	NO	Cable with connector M8, 3-pin, 0.2 m	IHM03-01BNSVR8K	1114531
				Cable, 3-wire, 2 m	IHM03-01BNSVU2K	1111030
		PNP	NO	2 x cable with 1 x male connector, M8, 4-pin, 0.3 m	IHM03-01BPSVR9KS01	1138376
				Cable with connector M8, 3-pin, 0.2 m	IHM03-01BPSVR8K	1108735
				Cable, 3-wire, 2 m	IHM03-01BPSVU2K	1101607

- **Product version:** IHM03
- **Installation type:** quasi-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 1.5 mm
- **Output function:** NO
- **Special features:** Visual adjustment indicator, triple sensing range
- **Connection type:** Cable, 3-wire, 2 m

Housing	Switching output	Type	Part no.
Standard design	NPN	IHM03-1B5NSVU2S	1103993
	PNP	IHM03-1B5PSVU2S	1103564
Short-body	NPN	IHM03-1B5NSVU2K	1103990
	PNP	IHM03-1B5PSVU2K	1108725

- **Product version:** IMM04
- **Cylindrical thread design:** M4
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Special features:** Visual adjustment indicator

Sensing range S_n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.6 mm	Standard design	NPN	NC	Cable, 3-wire, 2 m	IMM04-0B6N0VU2S	1114510
			NO	Cable, 3-wire, 2 m	IMM04-0B6NSVU2S	1114509
		PNP	NC	Cable, 3-wire, 2 m	IMM04-0B6POVU2S	1111252
			NO	Cable with connector M8, 3-pin, 0.2 m	IMM04-0B6PSVR8S	1108739
				Cable, 3-wire, 2 m	IMM04-0B6PSVU2S	1103630
1 mm	Standard design	NPN	NO	Cable, 3-wire, 2 m	IMM04-01BNSVU2S	1105618
		PNP	NC	Cable, 3-wire, 2 m	IMM04-01BP0VU2S	1111253
			NO	Cable with connector M8, 3-pin, 0.2 m	IMM04-01BPSVR8S	1108740
				Cable, 3-wire, 2 m	IMM04-01BPSVU2S	1101613
	Short-body	NPN	NO	Cable with connector M8, 3-pin, 0.2 m	IMM04-01BNSVR8K	1114511
				Cable, 3-wire, 2 m	IMM04-01BNSVU2K	1103233
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m	IMM04-01BPSVR8K	1108738
				Cable, 3-wire, 2 m	IMM04-01BPSVR8KS05	1140563
				Cable, 3-wire, 2 m	IMM04-01BPSVU2K	1101614

- **Product version:** IMM04
- **Cylindrical thread design:** M4
- **Installation type:** quasi-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 1.5 mm
- **Output function:** NO
- **Special features:** Visual adjustment indicator, triple sensing range
- **Connection type:** Cable, 3-wire, 2 m

Housing	Switching output	Type	Part no.
Standard design	NPN	IMM04-1B5NSVU2S	1103994
	PNP	IMM04-1B5PSVU2S	1103631
Short-body	NPN	IMM04-1B5NSVU2K	1103988
	PNP	IMM04-1B5PSVU2K	1103989

- **Product version:** IHM04
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Special features:** Visual adjustment indicator

Sensing range S_n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.8 mm	Standard design	NPN	NO	Cable, 3-wire, 2 m	IHM04-0B8NSVU2S	1105839
				Connector M8, 3-pin	IHM04-0B8NSVT0S	1107983
		PNP	NC	Cable, 3-wire, 2 m	IHM04-0B8POVU2S	1114512
				Cable with connector M8, 3-pin, 0.2 m	IHM04-0B8PSVR8S	1107732
			NO	Cable, 3-wire, 2 m	IHM04-0B8PSVU2S	1101824
				Connector M8, 3-pin	IHM04-0B8PSVT0S	1103977
1.5 mm	Standard design	NPN	NO	Cable, 3-wire, 2 m	IHM04-1B5NSVU2S	1101903
				Connector M8, 3-pin	IHM04-1B5NSVT0S	1107920
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m	IHM04-1B5PSVR8S	1108728
				Cable, 3-wire, 2 m	IHM04-1B5PSVU2S	1096869
				Connector M8, 3-pin	IHM04-1B5PSVT0S	1097330
	Short-body	NPN	NO	Cable, 3-wire, 2 m	IHM04-1B5NSVU2K	1103992
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m	IHM04-1B5PSVR8K	1108726
				Cable, 3-wire, 2 m	IHM04-1B5PSVU2K	1101608

- **Product version:** IHM04
- **Installation type:** quasi-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 2.5 mm
- **Output function:** NO
- **Special features:** Visual adjustment indicator, triple sensing range

Housing	Switching output	Connection type	Type	Part no.
Standard design	NPN	Connector M8, 3-pin	IHM04-2B5NSVT0S	1103995
	PNP	Cable with connector M8, 3-pin, 0.2 m	IHM04-2B5PSVR8S	1108729
		Cable, 3-wire, 2 m	IHM04-2B5PSVU2S	1103551
		Connector M8, 3-pin	IHM04-2B5PSVT0S	1108724
Short-body	NPN	Cable, 3-wire, 2 m	IHM04-2B5NSVU2K	1108013
	PNP	Cable with connector M8, 3-pin, 0.2 m	IHM04-2B5PSVR8K	1108727
		Cable, 3-wire, 2 m	IHM04-2B5PSVU2K	1103550

- **Product version:** IMM05
- **Cylindrical thread design:** M5
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire
- **Special features:** Visual adjustment indicator

Sensing range S_n	Housing	Switching output	Output function	Connection type	Type	Part no.
0.8 mm	Standard design	NPN	NC	Cable, 3-wire, 2 m	IMM05-0B8NOVU2S	1114516
				Connector M8, 3-pin	IMM05-0B8NOVT0S	1114523
			NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-0B8NSVR8S	1108732
				Cable, 3-wire, 2 m	IMM05-0B8NSVU2S	1103634
				Connector M8, 3-pin	IMM05-0B8NSVT0S	1114520
		PNP	NC	Cable, 3-wire, 2 m	IMM05-0B8POVU2S	1114515
				Connector M8, 3-pin	IMM05-0B8POVT0S	1111255
			NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-0B8PSVR8S	1111249
				Cable, 3-wire, 2 m	IMM05-0B8PSVU2S	1101831
				Connector M8, 3-pin	IMM05-0B8PSVT0S	1103984

Sensing range S _n	Housing	Switching output	Output function	Connection type	Type	Part no.
1.5 mm	Standard design	NPN	NC	Cable, 3-wire, 2 m	IMM05-1B5NOVU2S	1114518
				Connector M8, 3-pin	IMM05-1B5NOVT0S	1114527
			NO	Cable, 3-wire, 2 m	IMM05-1B5NSVU2S	1101904
				Connector M8, 3-pin	IMM05-1B5NSVT0S	1114526
		PNP	NC	Cable, 3-wire, 2 m	IMM05-1B5POVU2S	1111254
					IMM05-1B5POVU2SS02	1119900
				Connector M8, 3-pin	IMM05-1B5POVT0S	1111256
			NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-1B5PSVR8S	1108733
				Cable, 3-wire, 2 m	IMM05-1B5PSVU2S	1101013
				Connector M8, 3-pin	IMM05-1B5PSVT0S	1101611
	Short-body	NPN	NO	Cable, 3-wire, 2 m	IMM05-1B5NSVU2K	1105620
		PNP	NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-1B5PSVR8K	1108730
				Cable, 3-wire, 2 m	IMM05-1B5PSVU2K	1101612

- **Product version:** IMM05
- **Cylindrical thread design:** M5
- **Installation type:** quasi-flush
- **Electrical wiring:** DC 3-wire
- **Sensing range S_n :** 2.5 mm
- **Special features:** Visual adjustment indicator, triple sensing range

Housing	Switching output	Output function	Connection type	Type	Part no.
Standard design	NPN	NO	Connector M8, 3-pin	IMM05-2B5NSVT0S	1103987
	PNP	NC	Cable, 3-wire, 2 m	IMM05-2B5POVU2S	1114519
		NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-2B5PSVR8S	1108734
			Cable, 3-wire, 2 m	IMM05-2B5PSVU2S	1101832
			Connector M8, 3-pin	IMM05-2B5PSVT0S	1104202
Short-body	NPN	NO	Cable, 3-wire, 2 m	IMM05-2B5NSVU2K	1103981
	PNP	NO	Cable with connector M8, 3-pin, 0.2 m	IMM05-2B5PSVR8K	1108731
			Cable, 3-wire, 2 m	IMM05-2B5PSVU2K	1103563

- **Product version:** IHM06
- **Installation type:** flush
- **Electrical wiring:** DC 3-wire

Sensing range S_n	Housing	Switching output	Output function	Special features	Connection type	Type	Part no.
1.5 mm	Extremely short model	NPN	NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-1B5NSVW2G	1103298
					Connector M8, 3-pin	IHM06-1B5NSVT0G	1101120
		PNP	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-1B5POVW2G	1104484
					Cable, 3-wire, 2 m	IHM06-1B5PSVU2G	1104494
			NO	Visual adjustment indicator		IHM06-1B5PSVW2G	1099600
					Connector M8, 3-pin	IHM06-1B5PSVT0G	1101119
	Short-body	PNP	NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-1B5PSVU2K	1115211
						IHM06-1B5PSVW2K	1114598
					Connector M8, 3-pin	IHM06-1B5PSVT0K	1114596
2 mm	Extremely short model	NPN	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNOVW2G	1103980
					Connector M8, 3-pin	IHM06-02BNOVT0G	1101123
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNSVW2G	1103979
					Connector M8, 3-pin	IHM06-02BNSVT0G	1101126
		PNP	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BPOVW2G	1103978
					Connector M8, 3-pin	IHM06-02BPOVT0G	1101122

Sensing range S_n	Housing	Switching output	Output function	Special features	Connection type	Type	Part no.
	Standard design	NPN	NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BPSVW2G	1099599
					Connector M8, 3-pin	IHM06-02BPSVT0G	1101121
		NPN	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNOVW2S	1104492
					Connector M8, 3-pin	IHM06-02BNOVT0S	1101132
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNSVW2S	1104493
					Connector M8, 3-pin	IHM06-02BNSVT0S	1101131
		PNP	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BPOVW2S	1104491
					Connector M8, 3-pin	IHM06-02BPOVT0S	1101134
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BPSVU2S	1104490
						IHM06-02BPSVW2S	1101165
					Connector M8, 3-pin	IHM06-02BPSVT0S	1101133
	Short-body	NPN	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNOVW2K	1104488
					Connector M8, 3-pin	IHM06-02BNOVT0K	1101129
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BNSVW2K	1104489
					Connector M8, 3-pin	IHM06-02BNSVT0K	1101130
		PNP	NC	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-02BPOVW2K	1104487
					Connector M8, 3-pin	IHM06-02BPOVT0K	1101128
			NO	Visual adjustment indicator	Cable with Molex 2201-3077 male connector, socket housing, 7-pin, 2 m	IHM06-02BPSVW2KS02	1153152
					Cable, 3-wire, 2 m	IHM06-02BPSVU2K	1104486
						IHM06-02BPSVW2K	1101164
					Connector M8, 3-pin	IHM06-02BPSVT0K	1101127

Sensing range S_n	Housing	Switching output	Output function	Special features	Connection type	Type	Part no.
3 mm	Extremely short model	NPN	NC	Visual adjustment indicator, triple sensing range	Connector M8, 3-pin	IHM06-03BNOVT0G	1103986
			NO		Cable, 3-wire, 2 m	IHM06-03BNSVW2G	1107047
		PNP	NC		Connector M8, 3-pin	IHM06-03BNSVT0G	1103985
			NO		Connector M8, 3-pin	IHM06-03BPOVT0G	1103983
			NC		Cable, 3-wire, 2 m	IHM06-03BPSVW2G	1107049
			NO		Connector M8, 3-pin	IHM06-03BPSVT0G	1103982
		NPN	NO		Connector M8, 3-pin	IHM06-03BNSVT0S	1107051
			NO		Connector M8, 3-pin	IHM06-03BPSVT0S	1107050
	Standard design	NPN	NC		Connector M8, 3-pin	IHM06-03BNOVT0K	1104498
			NO		Cable, 3-wire, 2 m	IHM06-03BNSVW2K	1113394
			NC		Connector M8, 3-pin	IHM06-03BNSVT0K	1104496
			NO		Connector M8, 3-pin	IHM06-03BPOVT0K	1104497
		PNP	NC		Connector M8, 3-pin	IHM06-03BPSVT0K	1104495
			NO				
			NC				
			NO				

- **Product version:** IHM06
- **Installation type:** non-flush
- **Electrical wiring:** DC 3-wire

Sensing range S_n	Housing	Switching output	Output function	Special features	Connection type	Type	Part no.
4 mm	Standard design	NPN	NC	Visual adjustment indicator	Connector M8, 3-pin	IHM06-04NNOVTO5	1104504
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-04NNSVW2S	1104514
					Connector M8, 3-pin	IHM06-04NNSVTO5	1104503
		PNP	NC	Visual adjustment indicator	Connector M8, 3-pin	IHM06-04NPOVTO5	1104505
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-04NPSVW2S	1104515
					Connector M8, 3-pin	IHM06-04NPSVTO5	1104506
	Short-body	NPN	NC	Visual adjustment indicator	Connector M8, 3-pin	IHM06-04NNOVTOK	1104501
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-04NNSVW2K	1104513
					Connector M8, 3-pin	IHM06-04NNSVTOK	1104502
		PNP	NC	Visual adjustment indicator	Connector M8, 3-pin	IHM06-04NPOVTOK	1104500
			NO	Visual adjustment indicator	Cable, 3-wire, 2 m	IHM06-04NPSVW2K	1104512
					Connector M8, 3-pin	IHM06-04NPSVTOK	1104499

Sensing range S _n	Housing	Switching output	Output function	Special features	Connection type	Type	Part no.
6 mm	Standard design	NPN	NO	Visual adjustment indicator, triple sensing range	Connector M8, 3-pin	IHM06-06NNSVT0S	1113395
		PNP	NO		Connector M8, 3-pin	IHM06-06NPSVT0S	1114155
	Short-body	NPN	NC		Connector M8, 3-pin	IHM06-06NNOVT0K	1104511
			NO		Cable, 3-wire, 2 m	IHM06-06NNSVW2K	1106314
		PNP	NC		Connector M8, 3-pin	IHM06-06NNSVT0K	1104510
					Cable, 3-wire, 2 m	IHM06-06NPOVW2K	1108857
			NO		Connector M8, 3-pin	IHM06-06NPOVT0K	1104509
					Cable with connector M8, 3-pin, 0.15 m	IHM06-06NPSVRDKS01	1139255
					Cable with plug M8, 3-pin, with knurled nut, 0.2 m	IHM06-06NPSVR8K	1134492
			Cable, 3-wire, 2 m		IHM06-06NPSVW2K	1105591	
			Connector M8, 3-pin		IHM06-06NPSVT0K	1104507	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com