




SLG

Compact light grid for reliable object detection

SICK
Sensor Intelligence.



Technical data overview

Operating range	1.5 m ... 7 m (depends on variant)
Beam separation	40 mm
Optical light exit	Flat Slim (depends on variant)
Detection height	120 mm ... 1,400 mm (depends on variant)
Connection type	Cable with M8 male connector, 4-pin Cable open end, 4-wire Cable with M12 male connector, 4-pin (depends on variant)
Length of cable	0.2 m

Product description

The smart light grid product family includes smart area sensors, smart gate sensors and smart pick-to-light-sensor light grids. At only 8 mm x 25 mm, they fit nearly anywhere and can be embedded inside walls, doors, conveyors, and machines. Slim and flat versions are available. They can be ordered in 120 to 1,400 mm lengths in a plastic or aluminum housing. Auto-muting, the teach-in button and an alignment aid ensure longer operating time

At a glance

- Variable monitoring lengths from 120 mm to 1,400 mm (in 160 mm increments)
- Operating range 7 m
- Response time 18 ms
- Resolution 45 mm to 25 mm
- Order-picking with bright job LEDs on the sender and receiver sides
- IP 65 protection class
- Ambient light immunity up to 150,000 lux

Your benefits

- Small, slim, and sleek design enables easy integration into applications
- Capacitive teach-in button and LEDs make commissioning easier for complex solutions
- Slim and flat models offer flexible mounting options
- User-defined factory preset configuration or flexible configuration with teach-in button
- Optical synchronization eliminates the need to lay cables, thus saving time
- At only 8 mm x 25 mm, smart light grids fit nearly anywhere and can be embedded inside walls, doors, conveyors, and machines
- The teach-in button and auto-muting enable Plug & Play. The alignment aid and the "Click & Go" principle also enable faster installation.

Fields of application

- Courier express parcel, postal & cargo
- Warehouse & distribution
- Automotive
- Airport
- Building automation

Ordering information

Other models and accessories → www.sick.com/SLG

- **Optical light exit:** Flat
- **Aluminum stabilizer:** Without stabilizer
- **Parameterization:** Teach-in button

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Length of cable	Type	Part no.
40 mm	Cross beam active	3 m	120 mm	–	SAS4-F012P3PS1T01	1209637

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Length of cable	Type	Part no.
			280 mm	–	SAS4-F012P3PS1T09	1213348
					SAS4-F028N3PC1T03	1215354
					SAS4-F028N3PS1T03	1215355
					SAS4-F028P3TS1T09	1218883
			440 mm	–	SAS4-F044N3PS1T03	1220767
					SAS4-F060N3PS1T03	1216575
			600 mm	–	SAS4-F060P3TS1T01	1213486
					SAS4-F060P3TS1T0D	1213487
					SGS4-F092N3PS1T03	1220768
					SGS4-F092P3PS1T0D	1211195
	Parallel beam active	3 m	120 mm	–	SAS4-F012N3PS1T00	1208785
					SAS4-F012P3PS1T00	1207475
			280 mm	–	SAS4-F028N3PC1T00	1217241
					SAS4-F028N3PS1T00	1208786
					SAS4-F028P3PS1T00	1208171
					SAS4-F044N3PS1T00	1207761
			440 mm	–	SAS4-F044P3PS1T00	1045020
					SAS4-F044P3PS1T02	1218911
					SAS4-F044N3CS1TS42	1109979
				0.2 m	SAS4-F044N3CS1TS42	1109979
			600 mm	–	SAS4-F060N3PS1T00	1208787
					SAS4-F060P3PS1T00	1048058
			760 mm	–	SGS4-F076N3PS1T00	1208788
			920 mm	–	SGS4-F092N3PS1T00	1210021
			1,080 mm	–	SGS4-F108P3PS1T00	1214282
		7 m	920 mm	–	SGS4-F092P7PS1T00	1208151
			1,080 mm	–	SGS4-F108P7PS1T00	1047501

- **Optical light exit:** Flat
- **Aluminum stabilizer:** Without stabilizer
- **Parameterization:** none

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	1.5 m	280 mm	SPL-F280PPS1W05	1215336
		3 m	280 mm	SAS4-F028N3PC1W01	1214794
				SAS4-F028N3PC1W03	1215345
				SAS4-F028N3PS1W01	1214757
				SAS4-F028N3PS1W03	1215346

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
			600 mm	SAS4-F028N3TS1W01	1214704
				SAS4-F028P3TS1W01	1212737
				SAS4-F060N3PS1W07	1217811
				SGS4-F060P3TS1W01	1219158
			760 mm	SGS4-F076N3PC1W01	1214793
				SGS4-F076N3PS1W01	1214758
				SGS4-F076N3TS1W01	1214703
				SGS4-F076P3TS1W01	1219155
			1,400 mm	SGS4-F140P3PS1W03	1218519
		7 m	920 mm	SGS4-F092F7PC1W11	1215260
				SGS4-F092F7PS1W11	1215261
	Parallel beam active	1.5 m	120 mm	SPL-F120NPS1W04	1208550
				SPL-F120PPC1W04	1208391
				SPL-F120PPS1W04	1046128
				SPL-F120PTC1W04	1214312
			280 mm	SPL-F280PPS1W04	1046764
				SPL-F280PTC1W04	1210776
			440 mm	SPL-F440NPS1W04	1220891
				SPL-F440PPS1W04	1046314
		3 m	120 mm	SAS4-F012P3PS1W00	1208450
40 mm	Parallel beam active	3 m	120 mm	SAS4-F012P3PS1W02	1215171
			280 mm	SAS4-F028P3PS1W00	1211906
			440 mm	SAS4-F044N3PS1W06	1218544
			760 mm	SGS4-F076F3PS1W14	1209181
			920 mm	SGS4-F092N3PS1W04	1217539
				SGS4-F092P3PS1W00	1216881
			1,080 mm	SGS4-F108N3PS1W04	1217540
				SGS4-F108P3PS1W00	1045008
			1,240 mm	SGS4-F124N3PS1W06	1218543
			1,400 mm	SGS4-F140N3PS1W02	1218777

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
		7 m		SGS4-F140N3PS1W06	1219275
				SGS4-F140P3PS1W00	1045012
			120 mm	SAS4-F012P7PC1W0A	1214157
				SAS4-F012P7PS1W0A	1214158
			600 mm	SGS4-F060P7PC1W00	1221047
				SGS4-F060P7PS1W00	1209723
				SGS4-F060P7PS1W02	1214855
				SGS4-F060P7PS1WS23	1071895
			760 mm	SGS4-F076P7PS1W00	1209287
			920 mm	SGS4-F092N7PS1W00	1209012
				SGS4-F092P7PC1W02	1216546
				SGS4-F092P7PS1W00	1047211
				SGS4-F092P7PS1W02	1213765
				SGS4-F092P7PS1WS22	1068077
			1,080 mm	SGS4-F108P7PS1W00	1045010
				SGS4-F108P7PS1W02	1047500
			1,400 mm	SGS4-F140N7PS1W02	1218778
				SGS4-F140P7PC1W02	1214854
				SGS4-F140P7PS1W00	1045014
				SGS4-F140P7PS1W02	1211095

- **Optical light exit:** Flat
- **Aluminum stabilizer:** With stabilizer
- **Parameterization:** Teach-in button

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	600 mm	SGS4-F060P3PS2T03	1209955
			920 mm	SGS4-F092P3PS2T01	1219326
			1,080 mm	SGS4-F108P3PS2T01	1207780
				SGS4-F108P3PS2T03	1217445
				SGS4-F108P3TS2T01	1212533
			1,240 mm	SGS4-F124P3TS2T01	1214074
			1,400 mm	SGS4-F140P3TS2T01	1214075
		7 m	760 mm	SGS4-F076P7PS2T01	1113627

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
	Parallel beam active	3 m	1,240 mm	SGS4-F124P7PS2T01	1216886
			1,400 mm	SGS4-F140P7PS2T01	1210585
			120 mm	SAS4-F012P3PS2T00	1222131
			280 mm	SAS4-F028P3PS2T00	1207711
				SAS4-F028P3PS2T02	1214336
				SAS4-F028P3TS2T00	1212332
			440 mm	SAS4-F044P3TS2T00	1212690
			600 mm	SAS4-F060P3PS2T00	1209213
			920 mm	SGS4-F092N3PS2T00	1212947
				SGS4-F092P3PS2T00	1217733
		7 m	1,240 mm	SGS4-F124P3PS2T00	1048038
			1,400 mm	SGS4-F140P3PS2T00	1208809
			600 mm	SGS4-F060P7PS2T00	1217200
			760 mm	SGS4-F076E7PS2TA0	1212226
				SGS4-F076F7PS2TA0	1212270
			920 mm	SGS4-F092P7PC2T00	1221935
				SGS4-F092P7PS2T00	1209734
			1,080 mm	SGS4-F108P7PS2T00	1221936
			1,240 mm	SGS4-F124F7PS2T00	1220168
				SGS4-F124P7PS2T00	1216552

- **Optical light exit:** Flat
- **Aluminum stabilizer:** With stabilizer
- **Parameterization:** none

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	1.5 m	280 mm	SPL-F280PTS2W05	1211251
		3 m	120 mm	SAS4-F012P3PS2W0B	1214346
			280 mm	SAS4-F028P3PC2W0B	1214348
				SAS4-F028P3PS2W0B	1214347
			600 mm	SGS4-F060P3PS2W07	1119232
			760 mm	SGS4-F076E3PS2W03	1211230
	Parallel beam active	1.5 m	120 mm	SPL-F120PPC2W04	1211690
				SPL-F120PPS2W04	1047344
				SPL-F120PTS2W04	1212775
			280 mm	SPL-F280PPC2W04	1211691

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
				SPL-F280PPS2W04	1046996
				SPL-F280PTC2W04	1212649
				SPL-F280PTS2W04	1212648
			440 mm	SPL-F440PPC2W04	1211692
				SPL-F440PPS2W04	1211300
				SPL-F440PTS2W04	1213728
		3 m	280 mm	SAS4-F028P3PS2W00	1212083
			600 mm	SAS4-F060P3TS2W04	1218051
			920 mm	SGS4-F092P3PS2W0E	1216882
			1,080 mm	SGS4-F108P3PS2W02	1221834
				SGS4-F108P3PS2W04	1216770
				SGS4-F108P3PS2W0C	1216883
			1,240 mm	SGS4-F124P3PS2W00	1216884
				SGS4-F124P3PS2W0C	1216885
			1,400 mm	SGS4-F140P3PS2W02	1219372
				SGS4-F140P3PS2W0C	1216887
				SGS4-F140P3PS2WS40	1089786
		7 m	600 mm	SGS4-F060P7PS2W00	1218379
				SGS4-F060P7TS2W00	1216873
			1,080 mm	SGS4-F108P7PS2W00	1212430

- **Optical light exit:** Flat
- **Aluminum stabilizer:** With stabilizer

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	280 mm	SAS4-F028P3PS2T01	1108417

- **Optical light exit:** Slim
- **Aluminum stabilizer:** Without stabilizer
- **Parameterization:** Teach-in button

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	280 mm	SAS4-S028P3PS1T01	1214138
			440 mm	SAS4-S044N3PS1T0D	1209170
				SAS4-S044P3PS1T01	1211165

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.	
			600 mm	SAS4-S060N3PS1T0D	1209171	
				SAS4-S060P3PC1T01	1210509	
				SAS4-S060P3PS1T01	1210508	
				SAS4-S060P3PS1T0D	1210098	
			760 mm	SGS4-S076P3PS1T0D	1211268	
			920 mm	SGS4-S092P3PS1T01	1215420	
			1,080 mm	SGS4-S108P3PS1T07	1211642	
			1,240 mm	SGS4-S124N3PS1T0D	1209172	
			1,400 mm	SGS4-S140P3PS1T0D	1211269	
			7 m	1,080 mm	SGS4-S108P7PC1T07	1212305
		SGS4-S108P7PS1T07			1212304	
		Parallel beam active	3 m	120 mm	SAS4-S012N3PS1T00	1047009
					SAS4-S012P3PC1T00	1113785
					SAS4-S012P3PS1T00	1047364
	280 mm			SAS4-S028N3PS1T00	1207707	
				SAS4-S028P3PS1T00	1047063	
				SAS4-S028P3TS1T00	1113023	
	440 mm			SAS4-S044N3PS1T00	1207708	
		SAS4-S044P3PS1T00		1045019		
		600 mm		SAS4-S060N3PC1T00	1221215	
	40 mm	Parallel beam active		3 m	600 mm	SAS4-S060N3PS1T00
SAS4-S060P3PS1T00			1047587			
SGS4-S060F3PS1T00			1216888			
SGS4-S060F3TS1T00			1219785			
SGS4-S060F3TS1T12			1219920			
SGS4-S060N3PS1T00			1210029			
760 mm			SGS4-S076N3PS1T00		1210030	
			SGS4-S076P3PS1T00		1047092	
920 mm			SGS4-S092P3PS1T00		1208201	
1,080 mm			SGS4-S108F3PC1T00		1217939	

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
				SGS4-S108N3PS1T00	1208155
				SGS4-S108P3PS1T00	1209472
			1,240 mm	SGS4-S124P3PS1T00	1216899
			1,400 mm	SGS4-S140P3PS1T00	1047015
		7 m	440 mm	SAS4-S044N7PS1T00	1212438
				SAS4-S044P7PS1T00	1217729
			600 mm	SGS4-S060P7PS1T00	1210569
				SGS4-S076N7PS1T00	1209741
			760 mm	SGS4-S076P7PC1T0A	1215360
				SGS4-S076P7PS1T00	1211689
				SGS4-S076P7PS1T0A	1215361
				SGS4-S092P7PS1T00	1208200
			920 mm	SGS4-S092P7PS1T00	1208200
				SGS4-S108F7PS1T00	1216895
			1,080 mm	SGS4-S108F7TS1T00	1216897
				SGS4-S108P7PC1T00	1214159
				SGS4-S108P7PC1T0A	1214836
				SGS4-S108P7PS1T00	1209457
				SGS4-S108P7PS1T0A	1214837
				SGS4-S140F7PS1T00	1047077
				SGS4-S140F7PS1TA0	1211383

- **Optical light exit:** Slim
- **Aluminum stabilizer:** Without stabilizer
- **Parameterization:** none

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	120 mm	SAS4-S012P3PS1W05	1221134
				SAS4-S028N3PS1W0B	1119962
			280 mm	SAS4-S028P3PS1W07	1114849
				SAS4-S028P3TS1W01	1212766
				SAS4-S044P3PS1W05	1216994
			440 mm	SAS4-S044P3PS1W07	1220419
				SAS4-S060N3PS1W07	1219276
			600 mm	SAS4-S060P3PS1W0D	1210099
				SGS4-S060P3TS1W01	1218109
				SGS4-S076N3PS1W05	1217542
			760 mm	SGS4-S076P3PS1W01	1211895
				SGS4-S076P3TS1W01	1217734
				SGS4-S076P3TS1W03	1218243
				SGS4-S092P3PS1W05	1216892
			920 mm	SGS4-S092P3PS1W05	1216892

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	1,080 mm	SGS4-S108P3PC1W01	1217451
				SGS4-S108P3PS1W01	1211249
		7 m	280 mm	SAS4-S028P7PS1W01	1214753
				SAS4-S044P7PS1W01	1214754
			600 mm	SGS4-S060P7PS1W01	1214772
			920 mm	SGS4-S092F7PC1W11	1215259
				SGS4-S092F7PS1W11	1215258
			1,080 mm	SGS4-S108P7PC1W07	1212343
				SGS4-S108P7PS1W07	1212344
			1,240 mm	SGS4-S124P7PC1W07	1212462
				SGS4-S124P7PS1W07	1212463
	Parallel beam active	1.5 m	120 mm	SPL-S120NPS1W04	1213983
				SPL-S120PPC1W04	1211282
				SPL-S120PPS1W04	1046127
			280 mm	SPL-S280PPC1W04	1215571
				SPL-S280PPS1W04	1046763
				SPL-S280PTC1W04	1213545
				SPL-S280PTS1W04	1213544
			440 mm	SPL-S440NPS1W04	1047365
				SPL-S440PPS1W04	1046312
		3 m	120 mm	SAS4-S012N3PS1W00	1047014
				SAS4-S028N3PS1W00	1207704
			280 mm	SAS4-S028P3PS1W00	1212471
				SAS4-S028P3TC1W02	1222177
				SAS4-S044N3PS1W00	1207705
			600 mm	SAS4-S044P3PS1W00	1209581
				SAS4-S060N3PS1W00	1207706
				SAS4-S060N3PS1W02	1207752
				SAS4-S060P3PS1W00	1047525
				SGS4-S060F3PS1W14	1217672
40 mm	Parallel beam active	3 m	600 mm	SGS4-S060P3PS1W00	1216889
			760 mm	SGS4-S076F3PS1W14	1217673
				SGS4-S076P3PC1W0A	1216199
				SGS4-S076P3PS1W00	1046966
				SGS4-S076P3PS1W0A	1216200
			1,080 mm	SGS4-S108P3PS1W00	1045007
				SGS4-S108P3PS1W02	1209567
				SGS4-S108P3PS1W82	1045017
			1,400 mm	SGS4-S140P3PS1W00	1045011
		7 m	120 mm	SAS4-S012P7PS1W0A	1215547

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
			440 mm	SAS4-S044P7PC1W0A	1215546
				SAS4-S044P7PS1W0A	1215545
			600 mm	SGS4-S060P7PS1W00	1209722
				SGS4-S076P7PS1W00	1209288
			760 mm	SGS4-S076P7TC1W02	1211306
				SGS4-S076P7TS1W02	1212927
				SGS4-S092P7PS1W00	1208596
			920 mm	SGS4-S092P7TC1W02	1211305
				SGS4-S092P7TS1W02	1212928
			1,080 mm	SGS4-S108F7PC1WA0	1216893
				SGS4-S108F7PC1WA4	1216894
				SGS4-S108F7PS1WA4	1216896
				SGS4-S108P7PC1W00	1216898
				SGS4-S108P7PC1W0A	1215509
				SGS4-S108P7PS1W00	1045009
				SGS4-S108P7PS1W0A	1215508
				SGS4-S108P7TS1W02	1106095
			1,400 mm	SGS4-S140P7PS1W00	1045013
				SGS4-S140P7TC1W02	1213243
				SGS4-S140P7TS1W02	1213242

- **Optical light exit:** Slim
- **Aluminum stabilizer:** With stabilizer
- **Parameterization:** Teach-in button

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	3 m	120 mm	SAS4-S012P3PS2T05	1211982
				SAS4-S012P3PS2T09	1213424
			600 mm	SGS4-S060P3PS2T07	1214022
			920 mm	SGS4-S092P3PS2T07	1211757
			1,080 mm	SGS4-S108P3PS2T03	1210418
				SGS4-S108P3PS2T07	1207519
			1,240 mm	SGS4-S124P3PC2T07	1212489
				SGS4-S124P3PS2T07	1212490
40 mm	Cross beam active	3 m	1,400 mm	SGS4-S140N3TS2T03	1112709
			1,400 mm	SGS4-S140P3TS2T03	1215613
		7 m	760 mm	SGS4-S076P7PS2T03	1216477
			920 mm	SGS4-S092P7PS2T03	1216476
			1,080 mm	SGS4-S108P7PC2T09	1216724
				SGS4-S108P7PS2T03	1210883

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
	Parallel beam active	3 m		SGS4-S108P7PS2T09	1216723
			1,240 mm	SGS4-S124P7PS2T03	1221914
			1,400 mm	SGS4-S140P7PS2T03	1210782
			120 mm	SAS4-S012P3PS2T00	1210494
			280 mm	SAS4-S028P3PS2T00	1210592
				SAS4-S028P3PS2T02	1215926
			440 mm	SAS4-S044P3PS2T00	1211573
				SAS4-S044P3TS2T00	1212689
			600 mm	SAS4-S060P3PS2T0A	1209782
				SGS4-S060P3PS2T00	1213187
			760 mm	SGS4-S076P3PS2T00	1216327
				SGS4-S076P3TS2T00	1219142
			920 mm	SGS4-S092P3PS2T00	1208108
				SGS4-S092P3TS2T02	1212061
			1,080 mm	SGS4-S108P3TS2T00	1221852
			1,240 mm	SGS4-S124P3PS2T00	1211293
			1,400 mm	SGS4-S140P3PS2T00	1208109
		7 m	120 mm	SAS4-S012P7PC2T0A	1214835
				SAS4-S012P7PS2T0A	1214834
			440 mm	SAS4-S044P7PC2T0A	1214833
				SAS4-S044P7PS2T0A	1214832
			600 mm	SGS4-S060P7PS2T00	1215363
			920 mm	SGS4-S092P7TC2T00	1217024
				SGS4-S092P7TS2T00	1217023
			1,400 mm	SGS4-S140P7PS2T00	1208241

- **Optical light exit:** Slim
- **Aluminum stabilizer:** With stabilizer
- **Parameterization:** none

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
40 mm	Cross beam active	1.5 m	280 mm	SPL-S280PPS2W05	1212183
				SPL-S280PTS2W05	1211386
		3 m	280 mm	SAS4-S028P3TS2W0F	1216005
			440 mm	SAS4-S044P3TS2W01	1218216
			600 mm	SAS4-S044P3TS2W0F	1220838
				SGS4-S060P3PS2W0F	1215269
			760 mm	SGS4-S060P3TS2W0F	1215352
				SGS4-S076P3PS2W0F	1215270
			920 mm	SGS4-S076P3TS2W0F	1215353
				SGS4-S092F3TS2W11	1123567
			1,080 mm	SGS4-S108P3PS2W01	1211250
			1,240 mm	SGS4-S108P3PS2W03	1211901
				SGS4-S124P3PS2W01	1211391
			1,240 mm	SGS4-S124P3PS2W05	1211392
				SGS4-S060N7PS2W01	1209875
		7 m	600 mm	SGS4-S060N7PS2W01	1209875
40 mm	Cross beam active	7 m	1,080 mm	SGS4-S108F7TS2W17	1209503
	Parallel beam active	1.5 m	120 mm	SPL-S120PPS2W04	1211239
				SPL-S120PTS2W04	1213729
			280 mm	SPL-S280PPS2W04	1209197
				SPL-S280PTC2W04	1212659
				SPL-S280PTS2W04	1212658
				SPL-S440PPS2W04	1045018
			440 mm	SPL-S440PTS2W04	1213730
				SAS4-S012P3PS2W04	1208464
		3 m	440 mm	SAS4-S044P3PS2W00	1211104

Beam separation	Cross beam/ parallel beam	Operating range	Detection height	Type	Part no.
				SAS4-S044P3TS2W00	1219143
			600 mm	SAS4-S060P3PS2W0A	1209013
				SGS4-S060P3PS2W00	1216890
			760 mm	SGS4-S076P3PC1WS35	1077735
				SGS4-S076P3PS2W00	1209927
				SGS4-S076P3PS2W0C	1216891
				SGS4-S076P3TS2W00	1219141
			920 mm	SGS4-S092P3PS2W00	1214817
				SGS4-S092P3PS2W04	1209924
			1,080 mm	SGS4-S108P3PS2W04	1216918
				SGS4-S108P3PS2W06	1217486
			1,240 mm	SGS4-S124P3PS2W00	1047815
				SGS4-S124P3PS2W04	1047903
				SGS4-S124P3PS2W0C	1216900
			1,400 mm	SGS4-S140P3PS2W00	1216901
		7 m	120 mm	SAS4-S012P7PS2W0A	1215510
			440 mm	SAS4-S044P7PC2W0A	1215507
				SAS4-S044P7PS2W0A	1215506
			1,400 mm	SGS4-S140P7PS2W00	1211751
				SGS4-S140P7PS2W02	1211963

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com