



CDB405-001
CDB

JUNCTION BOXES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
CDB405-001	1027093

Other models and accessories → www.sick.com/CDB



Detailed technical data

Features

Brief description	Small connection module for 5-V hand-held scanners and ICR80x
Supported products	Mobile handheld scanners ICR80x
Cloning module support (CMC)	No
Supports display module (CMD)	No
Supports power supply module (CMP)	No
Supports fieldbus gateway (CMF)	No

Mechanics/electronics

Supply voltage	(18 V DC ... 30 V DC)
Power consumption	4 W
Housing	Polycarbonate
Enclosure rating	IP65
Protection class	III
Weight	250 g
Dimensions (L x W x H)	124.2 mm x 113.1 mm x 53.9 mm
Scanner connection	15-pin D-Sub HD female connector
Service plug	9-pin D-Sub plug (internal)

Interfaces

Serial	✓ , RS-232, RS-422, RS-485
Digital inputs	Depending on sensor connected
Digital outputs	Depending on sensor connected
Optical indicators	6 LED
Configuration software	SOPAS ET

Ambient data

Ambient operating temperature	0 °C ... +40 °C
--------------------------------------	-----------------

Storage temperature	-20 °C ... +70 °C
Permissible relative humidity	≤ 90 %, Non-condensing


Certificates

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
4Dpro	✓

Classifications

ECLASS 5.0	27242208
ECLASS 5.1.4	27242608
ECLASS 6.0	27242608
ECLASS 6.2	27242608
ECLASS 7.0	27242608
ECLASS 8.0	27242608
ECLASS 8.1	27242608
ECLASS 9.0	27242608
ECLASS 10.0	27242608
ECLASS 11.0	27242608
ECLASS 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	32151705


Dimensional drawing CDB620



Dimensions in mm (inch)

Recommended accessories

Other models and accessories → www.sick.com/CDB

	Brief description	Type	part no.
integration modules and adapters			
	<ul style="list-style-type: none">Description: External parameter memory for integration in CDB620/CDB650/CDM42x	CMC600-101	1042259

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com