



FLN-OSSD1000105

Flexi Loop

SAFE SERIES CONNECTION

SICK
Sensor Intelligence.



Ordering information

Type	part no.
FLN-OSSD1000105	1061709

Other models and accessories → www.sick.com/Flexi_Loop



Detailed technical data

Safety-related parameters

Safety integrity level	SIL 3 (IEC 61508)
Category	Category 4 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)
PFH_D (mean probability of a dangerous failure per hour)	0.76×10^{-9} (EN ISO 13849)
T_M (mission time)	20 years (EN ISO 13849)

Functions

Diagnostic and monitoring functions	
Cross-circuit	Monitoring via OSSD device
Short-circuit	Monitoring via OSSD device
Discrepancy errors	Monitoring via Flexi Loop node
Sequence errors	Monitoring via Flexi Loop node

Interfaces

Connection usage	
Safety device connection	For safety sensor with dual-channel OSSD outputs, With standard input
Flexi Loop input	To connect to a Flexi Loop predecessor node or to connect the Flexi Loop line to the Flexi Soft safety controller.
Flexi Loop output	To connect to a Flexi Loop successor node or to terminate the Flexi Loop line with the Flexi Loop terminator.
Connection type	
Safety device connection	Female connector M12, 5-pin
Flexi Loop input	Male connector M12, 5-pin
Flexi Loop output	Female connector M12, 5-pin
Number of non-safe inputs	1
Number of non-safe outputs	0
Power supply output for external devices	✓

Electrical data - Operating data

Protection class	III (EN 61140)
-------------------------	----------------

Type of supply voltage	PELV or SELV
Supply voltage V_s	24 V DC (16.8 V DC ... 30 V DC)
Power consumption	45 mA

Electrical data - OSSD inputs

Input voltage	HIGH	13 V DC ... 30 V DC
	LOW	-5 V DC ... 5 V DC
Input current	HIGH	3.5 mA ... 6.2 mA
	LOW	-2.5 mA ... 2.5 mA

Electrical data - Non-safe inputs

Switching voltage	HIGH	13 V DC ... 30 V DC
	LOW	0 V DC ... 5 V DC
Input current		≤ 6.2 mA

Electrical data - Power supply output for external devices

Supply voltage	24 V DC (16.8 V DC ... 30 V DC)
Output current	≤ 3.9 A

Mechanical data

Dimensions (W x H x D)	68.15 mm x 48 mm x 18 mm
Weight	28 g (± 5 %)

Ambient data

Enclosure rating	IP65 (EN 60529) IP67 (EN 60529)
Ambient operating temperature	-25 °C ... +55 °C
Storage temperature	-25 °C ... +70 °C

Certificates


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
UK-Type-Examination approval	✓
cULus certificate	✓
cTUVus certificate	✓
EC-Type-Examination approval	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Classifications

ECLASS 5.0	27371990
-------------------	----------


ECLASS 5.1.4	27371990
ECLASS 6.0	27371819
ECLASS 6.2	27371819
ECLASS 7.0	27371819
ECLASS 8.0	27371819
ECLASS 8.1	27371819
ECLASS 9.0	27371819
ECLASS 10.0	27371819
ECLASS 11.0	27371819
ECLASS 12.0	27371819
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	41113704

Dimensional drawing OSSD, EMSS



Dimensions in mm (inch)

PIN assignment



The FL_IN pin assignment is only relevant for the first loop node in a safe series connection when connected to Flexi Soft. Additional Flexi Loop nodes are connected to FL_OUT using standardized cables with M12 plug connectors.

Connection	Pin	Signal	Description	Color-coded connecting cable
FL_IN	1	VDC	24 V supply voltage	Brown
	2	DATA_OUT	Output to Flexi Soft input In +1	White
	3	GND	GND supply voltage	Blue
	4	SAFE_OUT	Safe cut-off signal, output to Flexi Soft input In	Black
	5	DATA_IN	Input from Flexi Soft output Xn	Gray
OSSD	1	VDC	24 V supply voltage for safety device	Brown
	2	OSSD1	Input OSSD 1	White
	3	GND	GND supply voltage for safety device	Blue
	4	OSSD2	Input OSSD 2	Black
	5	AUX_IN	Non-safe input	Gray

The colors listed apply when using pre-assembled cables (no guarantee).

Recommended accessories

Other models and accessories → www.sick.com/Flexi_Loop

	Brief description	Type	part no.
Mounting systems			
	<ul style="list-style-type: none"> Description: Flexi Loop fixing clip Dimensions (W x H x L): 15 mm x 32 mm x 21 mm Packing unit: 1 piece Suitable for: Flexi Loop 	C-Fix bracket	2068830

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com