


CDF600-2201

CDF

NETWORK DEVICES

SICK
Sensor Intelligence.



Ordering information

Type	part no.
CDF600-2201	1063390

Other models and accessories → www.sick.com/CDF



Detailed technical data

Features

Supported products	Lector series CLV61x - CLV65x CLV69x RFID read/write device Mobile handheld scanners
Cloning module support (CMC)	Integrated
Supports display module (CMD)	No
Supports power supply module (CMP)	No
Supports fieldbus gateway (CMF)	No

Mechanics/electronics

Supply voltage	(10 V DC ... 30 V DC)
Power consumption	< 5 W, if no sensor is connected and the digital input is not connected
Housing	Aluminum (unpainted)
Enclosure rating	IP65
Protection class	III
Weight	+ 690 g
Dimensions (L x W x H)	270.1 mm x 74.7 mm x 47.4 mm
Scanner connection	RS-232

Interfaces

PROFINET	✓ , RS-232
Function	PROFINET Dual Port
Data transmission rate	57.6 kBaud, 2-port Ethernet in accordance with IEEE 802.3 (baud rate 100 MBit/s, full-duplex transmission, 2-port switch, auto-negotiation, auto-crossover). Maximum data length is limited by the mode of communication (fragmentation protocol) to 4,000 bytes.
Serial	✓ , RS-232
Function	Service interface
Data transmission rate	57.6 kBaud

Digital inputs	1
Digital outputs	0
Optical indicators	8 LEDs
Configuration software	SOPAS ET

Ambient data

Electromagnetic compatibility (EMC)	EN61000-6-4:2018-02 / EN 61000-6-2:2005-08
Vibration resistance	EN 60068-2-6:2008-02
Shock resistance	EN 60068-2-27:2009-05
Ambient operating temperature	-35 °C ... +50 °C
Storage temperature	-35 °C ... +70 °C
Permissible relative humidity	< 90 %, Non-condensing

Certificates





EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Profinet certificate	✓

Classifications

ECLASS 5.0	27242208
ECLASS 5.1.4	27242608
ECLASS 6.0	27242608
ECLASS 6.2	27242608
ECLASS 7.0	27242608
ECLASS 8.0	27242608
ECLASS 8.1	27242608
ECLASS 9.0	27242608
ECLASS 10.0	27242608
ECLASS 11.0	27242608
ECLASS 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	32151705

Recommended accessories

Other models and accessories → www.sick.com/CDF

	Brief description	Type	part no.
connectors and cables			
	<ul style="list-style-type: none"> Description: USB 2.0, unshielded Connection type head A: Male connector, Micro-B, 4-pin, straight Connection type head B: Male connector, USB-A, 4-pin, straight Signal type: USB 2.0 Cable: 2 m, 4-wire 	YMUSA4-020VG4MUIA4	6036106
	<ul style="list-style-type: none"> Connection type head A: Male connector, M12, 5-pin, straight Connection type head B: Flying leads Signal type: Digital I/Os Cable: 2 m, PUR, halogen-free Description: Digital I/Os, unshielded Connection systems: Flying leads 	Connecting cable	6026133
device protection and care			
	<ul style="list-style-type: none"> Description: Protective cap with lock for power push-pull mounting frame, enclosure rating IP 65 	Protective cap	5327762
	<ul style="list-style-type: none"> Description: Protective cap with lock for PROFINET RJ45 push-pull mounting frame, enclosure rating IP 65 	Protective cap	5326204

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com