



# M2C-SX0340LA10

deTem

**SAFETY MULTIBEAM SENSORS**

**SICK**  
Sensor Intelligence.



Illustration may differ



### Ordering information

| Type           | part no. |
|----------------|----------|
| M2C-SX0340LA10 | 1093900  |

Other models and accessories → [www.sick.com/deTem](http://www.sick.com/deTem)

### Detailed technical data

#### Features

|                                    |                                                                                        |
|------------------------------------|----------------------------------------------------------------------------------------|
| <b>Product version</b>             | deTem2 Core Ex II 3GD                                                                  |
| <b>Application</b>                 | Explosive areas                                                                        |
| <b>Ex-approvals</b>                | ATEX for gas: II 3G Ex ec op is IIC T4 Gc<br>ATEX for dust: II 3D Ex tc IIIC T135°C Dc |
| <b>Functional principle</b>        | Sender/receiver                                                                        |
| <b>System part</b>                 | Sender                                                                                 |
| <b>Scanning range</b>              | 17 m                                                                                   |
| <b>Dimension of the light path</b> | Typical 0.5 m ... 17 m                                                                 |
| <b>Number of beams</b>             | 3                                                                                      |
| <b>Beam separation</b>             | 400 mm                                                                                 |
| <b>Response time</b>               | 20 ms                                                                                  |
| <b>Synchronization</b>             | Optical synchronization                                                                |
| <b>Items supplied</b>              | Sender                                                                                 |

#### Safety-related parameters

|                                                                           |                          |
|---------------------------------------------------------------------------|--------------------------|
| <b>Type</b>                                                               | Type 2 (IEC 61496-1)     |
| <b>Safety integrity level</b>                                             | SIL 1 (IEC 61508)        |
| <b>Category</b>                                                           | Category 2 (ISO 13849-1) |
| <b>Performance level</b>                                                  | PL c (ISO 13849-1)       |
| <b>PFH<sub>D</sub> (mean probability of a dangerous failure per hour)</b> | $3 \times 10^{-9}$       |
| <b>T<sub>M</sub> (mission time)</b>                                       | 20 years (ISO 13849-1)   |

|                                           |                                        |
|-------------------------------------------|----------------------------------------|
| <b>Safe state in the event of a fault</b> | At least one OSSD is in the OFF state. |
|-------------------------------------------|----------------------------------------|

## Interfaces

|                          |                  |
|--------------------------|------------------|
| <b>System connection</b> | Plug, M12, 5-pin |
| <b>Display elements</b>  | LEDs             |

## Electronics

|                                        |                                                 |
|----------------------------------------|-------------------------------------------------|
| <b>Protection class</b>                | III (IEC 61140)                                 |
| <b>Supply voltage <math>V_s</math></b> | 24 V DC (19.2 V DC ... 28.8 V DC) <sup>1)</sup> |
| <b>Residual ripple</b>                 | $\leq 10\%$ <sup>2)</sup>                       |
| <b>Power consumption</b>               | $\leq 50$ mA                                    |
| <b>Power consumption</b>               | $\leq 1.44$ W (DC)                              |

<sup>1)</sup> The external voltage supply must be capable of buffering brief mains voltage failures of 20 ms as specified in EN 60204-1. Suitable power supplies are available as accessories from SICK.

<sup>2)</sup> Within the limits of  $V_s$ .

## Mechanics

|                              |                           |
|------------------------------|---------------------------|
| <b>Dimensions</b>            | See dimensional drawing   |
| <b>Housing cross-section</b> | 38.7 mm x 45.6 mm         |
| <b>Material</b>              |                           |
| Housing                      | Aluminum extruded profile |
| <b>Weight</b>                | 800 g ( $\pm 50$ g)       |
| <b>Cable bend radius</b>     |                           |
| Stationary position          | $> 12$ x cable diameter   |
| Flexible use                 | $> 15$ x cable diameter   |

## Ambient data

|                                      |                                           |
|--------------------------------------|-------------------------------------------|
| <b>Enclosure rating</b>              | IP65 (IEC 60529)<br>IP67 (IEC 60529)      |
| <b>Ambient operating temperature</b> | 0 °C ... +55 °C                           |
| <b>Storage temperature</b>           | -30 °C ... +70 °C                         |
| <b>Air humidity</b>                  | 15 % ... 95 %, Non-condensing             |
| <b>Vibration resistance</b>          | 5 ... 150 Hz, 3,5 mm / 1 g (EN 60068-2-6) |
| <b>Shock resistance</b>              | 15 g / 6 ms (EN 60068-2-27)               |
| <b>Class</b>                         | 3M4 (IEC TR 60721-4-3)                    |

## Other information

|                      |                                |
|----------------------|--------------------------------|
| <b>Type of light</b> | Near-infrared (NIR), invisible |
|----------------------|--------------------------------|

## Certificates


|                                           |   |
|-------------------------------------------|---|
| <b>EU declaration of conformity</b>       | ✓ |
| <b>UK declaration of conformity</b>       | ✓ |
| <b>ACMA declaration of conformity</b>     | ✓ |
| <b>Moroccan declaration of conformity</b> | ✓ |
| <b>China RoHS</b>                         | ✓ |
| <b>UK-Type-Examination approval</b>       | ✓ |
| <b>IECEX certificate</b>                  | ✓ |

|                                                                              |   |
|------------------------------------------------------------------------------|---|
| <b>ULus approval</b>                                                         | ✓ |
| <b>cUL approval</b>                                                          | ✓ |
| <b>EC-Type-Examination approval</b>                                          | ✓ |
| <b>China EX Type-Examination certificate</b>                                 | ✓ |
| <b>Information according to Art. 3 of Data Act (Regulation EU 2023/2854)</b> | ✓ |

### Classifications

|                       |          |
|-----------------------|----------|
| <b>ECLASS 5.0</b>     | 27272703 |
| <b>ECLASS 5.1.4</b>   | 27272703 |
| <b>ECLASS 6.0</b>     | 27272703 |
| <b>ECLASS 6.2</b>     | 27272703 |
| <b>ECLASS 7.0</b>     | 27272703 |
| <b>ECLASS 8.0</b>     | 27272703 |
| <b>ECLASS 8.1</b>     | 27272703 |
| <b>ECLASS 9.0</b>     | 27272703 |
| <b>ECLASS 10.0</b>    | 27272703 |
| <b>ECLASS 11.0</b>    | 27272703 |
| <b>ECLASS 12.0</b>    | 27272703 |
| <b>ETIM 5.0</b>       | EC001832 |
| <b>ETIM 6.0</b>       | EC001832 |
| <b>ETIM 7.0</b>       | EC001832 |
| <b>ETIM 8.0</b>       | EC001832 |
| <b>UNSPSC 16.0901</b> | 46171620 |

## Dimensional drawing



Dimensions in mm (inch)

- ① Operating indicator
- ② Alignment indicator
- ③ Optical axis

| Number of beams | Beam separation S | Length L     |
|-----------------|-------------------|--------------|
| 2               | 500 (19.69)       | 672 (26.46)  |
| 3               | 400 (15.75)       | 972 (38.27)  |
| 4               | 300 (11.81)       | 1,072 (42.2) |

## Recommended accessories

Other models and accessories → [www.sick.com/deTem](http://www.sick.com/deTem)

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | Type          | part no. |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------|
| Safety relays                                                                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |               |          |
|    | <ul style="list-style-type: none"> <li>• <b>Applications:</b> Evaluation unit</li> <li>• <b>Compatible sensor types:</b> Safety sensors with OSSDs</li> <li>• <b>Connection type:</b> Front connector with spring terminals</li> <li>• <b>Restart interlock:</b> yes</li> <li>• <b>External device monitoring (EDM):</b> Integrated</li> <li>• <b>Outputs:</b> 2 enabling current paths (safe), 2 application diagnostic outputs (not safe), 1 test pulse output (not safe)</li> <li>• <b>Housing width:</b> 18 mm</li> </ul> | RLY3-OSSD200  | 1085344  |
|    | <ul style="list-style-type: none"> <li>• <b>Applications:</b> Evaluation unit</li> <li>• <b>Compatible sensor types:</b> Safety sensors with OSSDs</li> <li>• <b>Connection type:</b> Front connector with spring terminals</li> <li>• <b>Restart interlock:</b> yes</li> <li>• <b>External device monitoring (EDM):</b> Integrated</li> <li>• <b>Outputs:</b> 3 enabling current paths (safe), 2 application diagnostic outputs (not safe), 1 test pulse output (not safe)</li> <li>• <b>Housing width:</b> 18 mm</li> </ul> | RLY3-OSSD300  | 1099969  |
| Mounting systems                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |               |          |
|   | <ul style="list-style-type: none"> <li>• <b>Description:</b> QuickFix bracket for 2 devices (e.g. sender and receiver)</li> <li>• <b>Material:</b> Plastic</li> <li>• <b>Details:</b> Plastic</li> <li>• <b>Packing unit:</b> 4 pieces</li> </ul>                                                                                                                                                                                                                                                                             | BEF-3SHABPKU4 | 2098710  |
|  | <ul style="list-style-type: none"> <li>• <b>Description:</b> FlexFix bracket for 2 devices (e.g. sender and receiver), can be aligned <math>\pm 15^\circ</math>, including M5 screw</li> <li>• <b>Material:</b> Plastic</li> <li>• <b>Details:</b> Plastic</li> <li>• <b>Packing unit:</b> 4 pieces</li> </ul>                                                                                                                                                                                                                | BEF-1SHABPKU4 | 2066614  |

|                                                                                     | Brief description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | Type               | part no. |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|----------|
| connectors and cables                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |                    |          |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, A-coded</li> <li><b>Connection type head B:</b> Female connector, M12, 5-pin, A-coded</li> <li><b>Connection type head C:</b> Male connector, M12, 5-pin, A-coded</li> </ul>                                                                                                                                                                                       | DSC-1205T000025KMC | 6030664  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Male connector, M12, 5-pin, straight, A-coded</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 2 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>  | YF2A15-020UB5M2A15 | 2096009  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Male connector, M12, 5-pin, straight, A-coded</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>  | YF2A15-050UB5M2A15 | 2096010  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Male connector, M12, 5-pin, straight, A-coded</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 10 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul> | YF2A15-100UB5M2A15 | 2096011  |
|    | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 2 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>                                   | YF2A15-020UB5XLEAX | 2095617  |
|   | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 5 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>                                   | YF2A15-050UB5XLEAX | 2095618  |
|  | <ul style="list-style-type: none"> <li><b>Description:</b> Sensor/actuator cable, unshielded</li> <li><b>Connection type head A:</b> Female connector, M12, 5-pin, straight, A-coded</li> <li><b>Connection type head B:</b> Flying leads</li> <li><b>Signal type:</b> Sensor/actuator cable</li> <li><b>Cable:</b> 10 m, 5-wire, PUR, halogen-free</li> <li><b>Application:</b> Drag chain operation, Zones with oils and lubricants, Robot, Drag chain operation</li> </ul>                                  | YF2A15-100UB5XLEAX | 2095619  |

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)