



# HF transponder, cylinder

HF transponders

RFID TRANSPONDERS

**SICK**  
Sensor Intelligence.



### Ordering information

Type	part no.
HF transponder, cylinder	6067993

Other models and accessories → [www.sick.com/HF\\_transponders](http://www.sick.com/HF_transponders)

### Detailed technical data

#### Features

<b>Product segment</b>	RFID transponders, RFID
<b>Product</b>	HF transponders
<b>Scope</b>	Floor marking for AGVs (Automated Guided Vehicles), Transponder embedding
<b>Frequency band</b>	HF (13.56 MHz)
<b>Design</b>	Cylinders
<b>Housing material</b>	Epoxy
<b>Ambient operating temperature</b>	-5 °C ... +50 °C <sup>1)</sup>
<b>Storage temperature</b>	-5 °C ... +50 °C
<b>Housing color</b>	Blue
<b>IC type</b>	NXP ICODE SLIX
<b>Storage capacity</b>	896 Bit (28 x 4 Byte) (User Memory)
<b>IC data retention time</b>	< 10 years
<b>Mounting method</b>	Recessed
<b>Dimensions (W x H x L)</b>	7 mm x 14 mm
<b>Diameter</b>	7 mm
<b>Weight</b>	+ 1.44 g
<b>Reading range</b>	
	RFH505 1 cm <sup>2)</sup>
	RFH510 2 cm <sup>2)</sup>
	RFH515 3 cm <sup>2)</sup>
	RFH620 5.5 cm <sup>2)</sup>
	RFH630 14 cm <sup>2)</sup>

<sup>1)</sup> Max. temperature at which the RFID transponder can interact with the RFID read/write device.


<sup>2)</sup> Typical value; actual value depends on environmental conditions.

#### Classifications


<b>ECLASS 5.0</b>	27280401
<b>ECLASS 5.1.4</b>	27280401
<b>ECLASS 6.0</b>	27280401

<b>ECLASS 6.2</b>	27280401
<b>ECLASS 7.0</b>	27280401
<b>ECLASS 8.0</b>	27280401
<b>ECLASS 8.1</b>	27280402
<b>ECLASS 9.0</b>	27280402
<b>ECLASS 10.0</b>	27280402
<b>ECLASS 11.0</b>	27280402
<b>ECLASS 12.0</b>	27280402
<b>ETIM 5.0</b>	EC002593
<b>ETIM 6.0</b>	EC002998
<b>ETIM 7.0</b>	EC002998
<b>ETIM 8.0</b>	EC002998
<b>UNSPSC 16.0901</b>	52161523

### Instruction for installation



### Instruction for installation



## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

## WORLDWIDE PRESENCE:

Contacts and other locations –[www.sick.com](http://www.sick.com)