



DATA SHEET

WS/WE12L-2N430

W12
Photoelectric sensors

SICK

Sensor Intelligence

PHOTOELECTRIC SENSORS

WS/WE12L-2N430

ORDERING INFORMATION

| Type | part no. |
|----------------|----------|
| WS/WE12L-2N430 | 1018255 |

Further device versions and accessories at www.sick.com/W12



Illustration may differ



DETAILED TECHNICAL DATA

FEATURES

| | | |
|--------------------------------------|---|-----------------------------------|
| Functional principle | Through-beam photoelectric sensor | |
| Sensing range max. | 0 m ... 80 m | |
| Emitted beam | Light source | Laser ¹⁾ |
| | Type of light | Visible red light |
| | Light spot size (distance) | Ø 150 mm (60 m) |
| Key laser figures | Normative reference | EN 60825-1:2014, IEC 60825-1:2007 |
| | Laser class | 2 ^{2) 3)} |
| | Key LED figures | Wave length |
| Adjustment | None | |
| Special applications | Detecting small objects, Detection of objects moving at high speeds | |
| Items supplied | 2 x clamps BEF-KH-W12, incl. screws | |
| Part number of individual components | 2021722 WS12L-2D430 2021725 WE12L-2N430 | |

¹⁾ Average service life: 50,000 h at $T_u = +25\text{ °C}$.

²⁾ Pulse length 4 μs , max. pulse power < 5,0 mW.

³⁾ Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

SAFETY-RELATED PARAMETERS

| | |
|-------------------|-----------|
| MTTF _D | 308 years |
| DC _{avg} | 0 % |

| | |
|----------------------|----------|
| T_M (mission time) | 10 years |
|----------------------|----------|

ELECTRONICS

| | | | | | | | | | | | | | | | |
|-------------------------------|--|------|-----|-------------------------|----------------------------------|-----------------------------|---|-----------------------------|---|--------------------------|---------------|---------------|--------------------------------|---------------------|------------------------|
| Supply voltage U_B | 10 V DC ... 30 V DC ¹⁾ | | | | | | | | | | | | | | |
| Ripple | $< 5 V_{pp}$ ²⁾ | | | | | | | | | | | | | | |
| Current consumption, sender | $\leq 45 mA$ ³⁾ | | | | | | | | | | | | | | |
| Current consumption, receiver | $\leq 15 mA$ ³⁾ | | | | | | | | | | | | | | |
| Protection class | III | | | | | | | | | | | | | | |
| Digital output | <table border="0"> <tr> <td>Type</td> <td>NPN</td> </tr> <tr> <td>Switching mode selector</td> <td>Selectable via L/D control cable</td> </tr> <tr> <td>Signal voltage PNP HIGH/LOW</td> <td>$U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$</td> </tr> <tr> <td>Signal voltage NPN HIGH/LOW</td> <td>$U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$</td> </tr> <tr> <td>Output current I_{max}</td> <td>$\leq 100 mA$</td> </tr> <tr> <td>Response time</td> <td>$\leq 200 \mu s$ ⁴⁾</td> </tr> <tr> <td>Switching frequency</td> <td>2,500 Hz ⁵⁾</td> </tr> </table> | Type | NPN | Switching mode selector | Selectable via L/D control cable | Signal voltage PNP HIGH/LOW | $U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$ | Signal voltage NPN HIGH/LOW | $U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$ | Output current I_{max} | $\leq 100 mA$ | Response time | $\leq 200 \mu s$ ⁴⁾ | Switching frequency | 2,500 Hz ⁵⁾ |
| Type | NPN | | | | | | | | | | | | | | |
| Switching mode selector | Selectable via L/D control cable | | | | | | | | | | | | | | |
| Signal voltage PNP HIGH/LOW | $U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$ | | | | | | | | | | | | | | |
| Signal voltage NPN HIGH/LOW | $U_v - < 2.9 V, U_v V / 0 V \leq 1.5 V$ | | | | | | | | | | | | | | |
| Output current I_{max} | $\leq 100 mA$ | | | | | | | | | | | | | | |
| Response time | $\leq 200 \mu s$ ⁴⁾ | | | | | | | | | | | | | | |
| Switching frequency | 2,500 Hz ⁵⁾ | | | | | | | | | | | | | | |
| Circuit protection | A ⁶⁾ C ⁷⁾ D ⁸⁾ | | | | | | | | | | | | | | |

¹⁾ Limit values when operated in short-circuit protected network: max. 8 A.

²⁾ May not fall below or exceed U_v tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ A = V_s connections reverse-polarity protected.

⁷⁾ C = interference suppression.

⁸⁾ D = outputs overcurrent and short-circuit protected.

MECHANICS

| | | | | | |
|------------------------|--|---------|-------|--------------|---------------|
| Housing | Rectangular | | | | |
| Dimensions (W x H x D) | 15 mm x 49 mm x 41.5 mm | | | | |
| Connection | Male connector M12, 4-pin | | | | |
| Material | <table border="0"> <tr> <td>Housing</td> <td>Metal</td> </tr> <tr> <td>Front screen</td> <td>Plastic, PMMA</td> </tr> </table> | Housing | Metal | Front screen | Plastic, PMMA |
| Housing | Metal | | | | |
| Front screen | Plastic, PMMA | | | | |
| Weight | 260 g | | | | |

AMBIENT DATA


| | |
|-------------------------------|------------------------------|
| Enclosure rating | IP67 IP69K |
| Ambient operating temperature | -10 °C ... +50 °C |
| Ambient temperature, storage | -25 °C ... +75 °C |
| UL File No. | NRKH.E181493 & NRKH7.E181493 |

CERTIFICATES

| | |
|------------------------------|---|
| EU declaration of conformity | ✓ |
| UK declaration of conformity | ✓ |

| | |
|--|---|
| ACMA declaration of conformity | ✓ |
| Moroccan declaration of conformity | ✓ |
| China RoHS | ✓ |
| cULus certificate | ✓ |
| Laser safety (IEC 60825-1) certificate | ✓ |


DIMENSIONAL DRAWING WL12L-2, WS/WE12L-2



Dimensions in mm (inch)


- ① Operating indicator, green
- ② LED reception indicator, yellow
- ③ Center of optical axis
- ④ M4 threaded mounting hole - 4 mm depth
- ⑤ Mounting hole, Ø 4.2 mm
- ⑥ Focal adjustment
- ⑦ sensitivity control

ADJUSTMENTS WS/WE12L-2




- ① status indicator (WS, top only)
- ⑥ Focal adjustment (WS)

ADJUSTMENTS




- ② LED signal strength indicator (WE)
- ⑦ Sensitivity adjustment (WE)

CONNECTION TYPE




CONNECTION DIAGRAM CD-077




- ① sender
- ② receiver

CHARACTERISTIC CURVE WS/WE12L-2, 80 M



SENSING RANGE DIAGRAM WS/WE12L-2, 80 M



■ Sensing range/sensing range typ. max.

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1018255



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence