



DATA SHEET

WL12L-2P130

W12
Photoelectric sensors

SICK

Sensor Intelligence

PHOTOELECTRIC SENSORS

WL12L-2P130

ORDERING INFORMATION

Type	part no.
WL12L-2P130	1022041

Further device versions and accessories at www.sick.com/W12



Illustration may differ



DETAILED TECHNICAL DATA

FEATURES

Functional principle	Photoelectric retro-reflective sensor	
Functional principle detail	Without reflector minimum distance (autocollimation/coaxial optics)	
Sensing range max.	0 m ... 18 m ¹⁾	
Polarisation filter	Yes	
Emitted beam	Light source	Laser ²⁾
	Type of light	Visible red light
	Light spot size (distance)	Ø 0.8 mm (300 mm)
Key laser figures	Normative reference	EN 60825-1:2014, IEC 60825-1:2007
	Laser class	2 ^{3) 4)}
Key LED figures	Wave length	650 nm
Adjustment	Potentiometer	
Special applications	Detecting small objects, Detection of objects moving at high speeds	
Items supplied	2 x clamps BEF-KH-W12, incl. screws	

¹⁾ Reflector PL80A.

²⁾ Average service life: 50,000 h at T_v = +25 °C.

³⁾ Pulse length 4 µs, max. pulse power < 5,0 mW.

⁴⁾ Do not intentionally look into the laser beam. Never point the laser beam at people's eyes.

SAFETY-RELATED PARAMETERS

MTTF _D	404 years
DC _{avg}	0 %
T _M (mission time)	10 years

ELECTRONICS

Supply voltage U _B	10 V DC ... 30 V DC ¹⁾																
Ripple	< 5 V _{pp} ²⁾																
Current consumption	55 mA ³⁾																
Protection class	III																
Digital output	<table border="0"> <tr> <td>Type</td> <td>PNP ⁴⁾ NPN ⁵⁾</td> </tr> <tr> <td>Switching mode</td> <td>Light switching, Dark switching ^{4) 5)}</td> </tr> <tr> <td>Switching mode selector</td> <td>Selectable via L/D control cable</td> </tr> <tr> <td>Signal voltage PNP HIGH/LOW</td> <td>U_v - < 2.9 V, U_v V / 0 V <= 1.5 V</td> </tr> <tr> <td>Signal voltage NPN HIGH/LOW</td> <td>U_v - < 2.9 V, U_v V / 0 V <= 1.5 V</td> </tr> <tr> <td>Output current I_{max}</td> <td>≤ 100 mA</td> </tr> <tr> <td>Response time</td> <td>≤ 200 μs ⁶⁾</td> </tr> <tr> <td>Switching frequency</td> <td>2,500 Hz ⁷⁾</td> </tr> </table>	Type	PNP ⁴⁾ NPN ⁵⁾	Switching mode	Light switching, Dark switching ^{4) 5)}	Switching mode selector	Selectable via L/D control cable	Signal voltage PNP HIGH/LOW	U _v - < 2.9 V, U _v V / 0 V <= 1.5 V	Signal voltage NPN HIGH/LOW	U _v - < 2.9 V, U _v V / 0 V <= 1.5 V	Output current I _{max}	≤ 100 mA	Response time	≤ 200 μs ⁶⁾	Switching frequency	2,500 Hz ⁷⁾
Type	PNP ⁴⁾ NPN ⁵⁾																
Switching mode	Light switching, Dark switching ^{4) 5)}																
Switching mode selector	Selectable via L/D control cable																
Signal voltage PNP HIGH/LOW	U _v - < 2.9 V, U _v V / 0 V <= 1.5 V																
Signal voltage NPN HIGH/LOW	U _v - < 2.9 V, U _v V / 0 V <= 1.5 V																
Output current I _{max}	≤ 100 mA																
Response time	≤ 200 μs ⁶⁾																
Switching frequency	2,500 Hz ⁷⁾																
Circuit protection	A ⁸⁾ C ⁹⁾ D ¹⁰⁾																

¹⁾ Limit values when operated in short-circuit protected network: max. 8 A.

²⁾ May not fall below or exceed U_v tolerances.

³⁾ Without load.

⁴⁾ 0 V or not connected, light switching.

⁵⁾ U_v, dark switching.

⁶⁾ Signal transit time with resistive load.

⁷⁾ With light/dark ratio 1:1.

⁸⁾ A = V_g connections reverse-polarity protected.

⁹⁾ C = interference suppression.

¹⁰⁾ D = outputs overcurrent and short-circuit protected.

MECHANICS

Housing	Rectangular						
Dimensions (W x H x D)	15 mm x 49 mm x 41.5 mm						
Connection	Cable, 4-wire, 2 m						
Connection detail	<table border="0"> <tr> <td>Length of cable (L)</td> <td>2 m</td> </tr> </table>	Length of cable (L)	2 m				
Length of cable (L)	2 m						
Material	<table border="0"> <tr> <td>Housing</td> <td>Metal</td> </tr> <tr> <td>Front screen</td> <td>Plastic, PMMA</td> </tr> <tr> <td>Cable</td> <td>Plastic, PVC</td> </tr> </table>	Housing	Metal	Front screen	Plastic, PMMA	Cable	Plastic, PVC
Housing	Metal						
Front screen	Plastic, PMMA						
Cable	Plastic, PVC						

AMBIENT DATA

Enclosure rating	IP67 IP69K
------------------	---------------


PHOTOELECTRIC SENSORS - WL12L-2P130

Ambient operating temperature	-10 °C ... +50 °C
Ambient temperature, storage	-25 °C ... +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

CERTIFICATES

EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
Moroccan declaration of conformity	✓
China RoHS	✓
cULus certificate	✓
Laser safety (IEC 60825-1) certificate	✓


DIMENSIONAL DRAWING WL12L-2, WS/WE12L-2



Dimensions in mm (inch)


- ① Operating indicator, green
- ② LED reception indicator, yellow
- ③ Center of optical axis
- ④ M4 threaded mounting hole - 4 mm depth
- ⑤ Mounting hole, Ø 4.2 mm
- ⑥ Focal adjustment
- ⑦ sensitivity control

ADJUSTMENTS WL12L-2




- ① Operating indicator, green
- ② LED reception indicator, yellow
- ⑥ Focal adjustment
- ⑦ sensitivity control


CONNECTION TYPE



CONNECTION DIAGRAM CD-089




CHARACTERISTIC CURVE WL12L-2, 18 M



- ① Reflector PL80A
- ② Reflector PL50A
- ③ Reflective tape Diamond Grade

SENSING RANGE DIAGRAM WL12L-2, 18 M



■ Sensing range ■ Sensing range typ. max.

- ① Reflector PL80A
- ② Reflector PL50A
- ③ Reflector PL40A
- ④ Reflector P250
- ⑤ Reflector PL30A
- ⑥ Reflector PL20A
- ⑦ Reflective tape Diamond Grade

Further information as well as suitable accessories, example applications and downloads such as CAD dimensional models, operating instructions and software can be found at www.sick.com/1022041



SICK AG
WALDKIRCH
GERMANY
SICK.COM

SICK AT A GLANCE

SICK is a leading global technology company for intelligent sensors and integrated solutions in industrial automation. Our technologies set benchmarks, making your industrial processes more efficient, safer and more sustainable – both in logistics and manufacturing operations.

SICK combines sensor intelligence with industry expertise and certified consulting services. We provide the ideal foundation for scalable as well as tailor-made automation solutions and create added value along the entire value chain. Our close partnerships with our customers are more than just a promise: Together, we optimize productivity, improve quality, protect health and safety, and help build a sustainable future. All with empathy and trust.

Since 1946, we have been developing innovative technologies with passion and a pioneering spirit. With a global network in around 40 countries, SICK has a global presence and is always close by. The company's headquarters are located in Waldkirch near Freiburg, Germany. Our customers benefit from our understanding of both local and global requirements, which enables us to deliver tailor-made solutions

SICK
Sensor Intelligence