



RZT6-03ZUS-KW0

CYLINDER SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
RZT6-03ZUS-KW0	1025522

Other models and accessories → www.sick.com/

Detailed technical data

Features

Cylinder type	T-slot
Cylinder types with adapter	Profile cylinder Tie rod cylinder Round body cylinder Dovetail groove cylinder SMC rail CDQ2 SMC rail ECDQ2
Housing length	31.5 mm
Switching output	Reed
Switching output detail	Reed
Switching frequency	400 Hz
Output function	NO
Electrical wiring	AC/DC 2-wire
Enclosure rating	IP67 ¹⁾

¹⁾ According to EN 60529.

Mechanics/electronics

Supply voltage	10 V AC/DC ... 120 V AC/DC
Voltage drop	≤ 3.5 V
Continuous current I_a	≤ 100 mA
Switching capacity	≤ 6 W
Protection class	II ^{1) 2) 3)}
Response sensitivity, typ.	3 mT
Overrun distance, typ.	9 mm
Hysteresis, typ.	> 0.5 mT
Reproducibility	≤ 0.1 mT ⁴⁾

¹⁾ Rated voltage AC (effective) / DC 120 V.

²⁾ The sensor may only be used when mounted as a complete unit in the slot.

³⁾ Overvoltage category II.

⁴⁾ Supply voltage U_B and constant ambient temperature T_a.

Status indicator LED	Yes
Ambient operating temperature	-30 °C ... +80 °C
Shock and vibration resistance	30 g, 11 ms / 10 ... 55 Hz, 1 mm
EMC	According to EN 60947-5-2
Connection type	Cable, 2-wire, 2 m
Connection type Detail	
Conductor cross section	0.12 mm ²
Material	
Housing	Plastic
Cable	PVC
UL File No.	NRKH.E181493

1) Rated voltage AC (effective) / DC 120 V.

2) The sensor may only be used when mounted as a complete unit in the slot.

3) Overvoltage category II.

4) Supply voltage U_B and constant ambient temperature T_a .


Classifications

ECLASS 5.0	27270104
ECLASS 5.1.4	27270104
ECLASS 6.0	27270104
ECLASS 6.2	27270104
ECLASS 7.0	27270104
ECLASS 8.0	27270104
ECLASS 8.1	27270104
ECLASS 9.0	27270104
ECLASS 10.0	27270104
ECLASS 11.0	27270104
ECLASS 12.0	27274301
ETIM 5.0	EC002544
ETIM 6.0	EC002544
ETIM 7.0	EC002544
ETIM 8.0	EC002544
UNSPSC 16.0901	39122230


Connection type



Connection diagram Cd-037



Dimensional drawing Cable



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com