




ADAPT-PB-WI-MLG

Bus adapters

INTEGRATION MODULES AND ADAPTERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
ADAPT-PB-WI-MLG	1027901

Other models and accessories → www.sick.com/Bus_adapters

Detailed technical data


Features

Accessory group	Bus adapters
-----------------	--------------

Classifications

ECLASS 5.0	27279202
ECLASS 5.1.4	27279202
ECLASS 6.0	27279202
ECLASS 6.2	27279202
ECLASS 7.0	27279202
ECLASS 8.0	27279202
ECLASS 8.1	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ETIM 5.0	EC001020
ETIM 6.0	EC001020
ETIM 7.0	EC001020
ETIM 8.0	EC001020
UNSPSC 16.0901	31163032


Dimensional drawing



Dimensions in mm (inch)


- ① PROFIBUS OUT M12, 5-pin
- ② MLG receiver
- ③ MLG connection
- ④ PROFIBUS IN M12, 5-pin

Connection type



- ① MLG sender
- ② MLG receiver
- ③ Connection cable
- ④ Supply Q1
- ⑤ T-piece
- ⑥ MLG connection
- ⑦ PROFIBUS IN
- ⑧ PROFIBUS OUT
- ⑨ PROFIBUS adapter angled

Anschlusschema



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com