

WTF12-3N2433

W12-3

**SMALL PHOTOELECTRIC SENSORS** 





# Ordering information

Туре	Part no.
WTF12-3N2433	1041409

Included in delivery: BEF-KH-W12 (2)

Other models and accessories → www.sick.com/W12-3

Illustration may differ



### Detailed technical data

### **Features**

Functional principle	Photoelectric proximity sensor
Functional principle detail	Foreground suppression
Sensing range max.	30 mm 175 mm <sup>1)</sup>
Sensing range	30 mm 175 mm
Emitted beam	
Light source	LED <sup>2)</sup>
Type of light	Visible red light
Light spot size (distance)	Ø 2 mm (60 mm)
Key LED figures	
Wave length	640 nm
Adjustment	Double teach-in button
Special applications	Detecting flat objects
Items supplied	2 x clamps BEF-KH-W12, incl. screws

 $<sup>^{1)}</sup>$  Object with 90% remission (based on standard white, DIN 5033).

# Safety-related parameters

MTTF <sub>D</sub>	747 years
DC <sub>avg</sub>	0 %

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at TU = +25 °C.

### Electrical data

Supply voltage $\mathbf{U}_{\mathrm{B}}$	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	45 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	NPN
Switching mode	Light/dark switching
Signal voltage NPN HIGH/LOW	Approx. VS / < 2.5 V
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 330 μs <sup>4)</sup>
Switching frequency	1,500 Hz <sup>5)</sup>
Output function	Complementary
Circuit protection	A <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

### Mechanical data

Housing	Rectangular
Dimensions (W x H x D)	15.6 mm x 48.5 mm x 42 mm
Connection	Male connector M12, 4-pin
Material	
Housing	Metal
Front screen	Plastic, PMMA
Weight	120 g

# Ambient data

Enclosure rating	IP66 IP67
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

### Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904

 $<sup>^{2)}</sup>$  May not exceed or fall below  $U_{\nu}$  tolerances.

<sup>&</sup>lt;sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.


# WTF12-3N2433 | W12-3

SMALL PHOTOELECTRIC SENSORS

ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

# Adjustments

WTB12-3, WTF12-3, double teach-in button



- 4 LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- ® Sensing range adjustment: double teach-in button

# Connection type




## Connection diagram

### Cd-083


### Characteristic curve

WTF12-3, 175 mm



- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor


# Sensing range diagram



- Sensing range
- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

### Dimensional drawing (Dimensions in mm (inch))

### WTF12-3, Single teach-in button



- ① Standard direction of the material being detected
- ② Optical axis, receiver
- 3 Optical axis, sender
- ④ LED indicator green: Supply voltage active
- (5) LED indicator yellow: Status of received light beam
- 6 M4 threaded mounting hole, 4 mm deep
- Mounting hole, Ø 4.2 mm
- ® Sensing range adjustment: potentiometer
- Connection

#### Recommended accessories

Other models and accessories → www.sick.com/W12-3

	Brief description	Туре	Part no.
Plug connect	ors and cables		
•	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-G	6007302

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

