

# WTB12-3P2431T01

W12 Teflon

**SMALL PHOTOELECTRIC SENSORS** 







#### Ordering information

Туре	Part no.
WTB12-3P2431T01	1041414

Other models and accessories → www.sick.com/W12\_Teflon

#### Detailed technical data

#### **Features**

SIRIC® invented by SICK

Para all and a date	Photos de strik marriarita e a conse
Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Sensing range max.	20 mm 350 mm <sup>1)</sup>
Sensing range	20 mm 350 mm
Emitted beam	
Light source	LED <sup>2)</sup>
Type of light	Visible red light
Light spot size (distance)	Ø 6 mm (200 mm)
Key LED figures	
Wave length	640 nm
Adjustment	Potentiometer, 5 turns
Special applications	Hygienic and washdown zones

 $<sup>^{1)}</sup>$  Object with 90% remission (based on standard white, DIN 5033).

#### Safety-related parameters

MTTF <sub>D</sub>	728 years
DC <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at  $\rm T_U$  = +25 °C.

#### Electrical data

Supply voltage $\mathbf{U}_{\mathrm{B}}$	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	45 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	PNP
Switching mode	Light/dark switching
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 330 µs <sup>4)</sup>
Switching frequency	1,500 Hz <sup>5)</sup>
Output function	Complementary
Circuit protection	A <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>

 $<sup>^{1)}\,\</sup>mathrm{Limit}$  values when operated in short-circuit protected network: max. 8 A.

#### Mechanical data

Housing	Rectangular
Dimensions (W x H x D)	15.6 mm x 48.5 mm x 42 mm
Connection	Male connector M12, 4-pin
Material	
Housing	PTFE coating
Weight	120 g

#### Ambient data

Enclosure rating	IP66 IP67 IP69K
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

#### Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

<sup>&</sup>lt;sup>6)</sup> A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

<sup>8)</sup> D = outputs overcurrent and short-circuit protected.

# WTB12-3P2431T01 | W12 Teflon

SMALL PHOTOELECTRIC SENSORS

ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

# Connection type



### Connection diagram

Cd-083

#### Recommended accessories

Other models and accessories → www.sick.com/W12\_Teflon

	Brief description	Туре	Part no.
Plug connect	ors and cables		
Pio .	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235

# WTB12-3P2431T01 | W12 Teflon SMALL PHOTOELECTRIC SENSORS

Brief description	Туре	Part no.
<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-G	6009932

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

