

SICK Sensor Intelligence.

SMALL PHOTOELECTRIC SENSORS

SMALL PHOTOELECTRIC SENSORS



Ordering information

Туре	Part no.
WTF12-3P2443	1041401

Included in delivery: BEF-KH-W12 (2)

Other models and accessories → www.sick.com/W12-3





Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Foreground suppression
Sensing range max.	30 mm 500 mm ¹⁾
Sensing range	30 mm 500 mm
Emitted beam	
Light source	LED ²⁾
Type of light	Visible red light
Light spot size (distance)	Ø 7 mm (300 mm)
Key LED figures	
Wave length	640 nm
Adjustment	Single teach-in button
Items supplied	2 x clamps BEF-KH-W12, incl. screws

 $^{1)}$ Object with 90% remission (based on standard white, DIN 5033).

 $^{2)}$ Average service life: 100,000 h at T_U = +25 °C.

Safety-related parameters

MTTFD	810 years
DC _{avg}	0 %

SMALL PHOTOELECTRIC SENSORS

Electrical data

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	45 mA ³⁾
Protection class	III
Digital output	
Туре	PNP
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	> Uv - 2,5 V / ca. 0 V
Output current I _{max.}	≤ 100 mA
Response time	≤ 330 µs ⁴⁾
Switching frequency	1,500 Hz ⁵⁾
Output function	Complementary
Circuit protection	A ⁶⁾ C ⁷⁾ D ⁸⁾

 $^{1)}$ Limit values when operated in short-circuit protected network: max. 8 A.

²⁾ May not exceed or fall below U_v tolerances.

³⁾ Without load.

 $^{\rm 4)}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

⁶⁾ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.

 $^{(8)}$ D = outputs overcurrent and short-circuit protected.

Mechanical data

Housing	Rectangular
Dimensions (W x H x D)	15.6 mm x 48.5 mm x 42 mm
Connection	Male connector M12, 4-pin
Material	
Housing	Metal
Front screen	Plastic, PMMA
Weight	120 g

Ambient data

Enclosure rating	IP66 IP67
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

Classifications


ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904

SMALL PHOTOELECTRIC SENSORS

ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Adjustments

WTB12-3, WTF12-3, double teach-in button



- ④ LED indicator green: Supply voltage active
- (5) LED indicator yellow: Status of received light beam
- (a) Sensing range adjustment: double teach-in button

Connection type




Connection diagram

Cd-083



Characteristic curve


WTF12-3, 500 mm



- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on white, 90% remission factor

Sensing range diagram

WTF12-3, 500 mm




Sensing range

- 1 Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- ③ Sensing range on white, 90% remission factor

SMALL PHOTOELECTRIC SENSORS

Dimensional drawing (Dimensions in mm (inch))

WTF12-3, Single teach-in button



- ① Standard direction of the material being detected
- Optical axis, receiver
- ③ Optical axis, sender
- ④ LED indicator green: Supply voltage active
- 5 LED indicator yellow: Status of received light beam
- 6 M4 threaded mounting hole, 4 mm deep
- ⑦ Mounting hole, Ø 4.2 mm
- ③ Sensing range adjustment: potentiometer
- ③ Connection

Recommended accessories

Other models and accessories -> www.sick.com/W12-3

	Brief description	Туре	Part no.	
Plug connecto	Plug connectors and cables			
N C	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235	
	 Connection type head A: Male connector, M12, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² 	STE-1204-G	6009932	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

