

WTB12-3P2413

W12-3

**SMALL PHOTOELECTRIC SENSORS** 





# Ordering information

Туре	Part no.
WTB12-3P2413	1041423

Included in delivery: BEF-KH-W12 (2)

Other models and accessories → www.sick.com/W12-3

Illustration may differ



#### Detailed technical data

#### **Features**

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Sensing range max.	20 mm 600 mm <sup>1)</sup>
Sensing range	20 mm 600 mm
Emitted beam	
Light source	LED <sup>2)</sup>
Type of light	Infrared light
Light spot size (distance)	15 mm x 15 mm (200 mm)
Key LED figures	
Wave length	850 nm
Adjustment	Double teach-in button
Items supplied	2 x clamps BEF-KH-W12, incl. screws

 $<sup>^{1)}</sup>$  Object with 90% remission (based on standard white, DIN 5033).

# Safety-related parameters

MTTF <sub>D</sub>	937 years
DC <sub>avg</sub>	0 %

<sup>&</sup>lt;sup>2)</sup> Average service life: 100,000 h at  $T_U$  = +25 °C.

#### Electrical data

Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	55 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	PNP
Switching mode	Light/dark switching
Signal voltage PNP HIGH/LOW	> Uv - 2,5 V / ca. 0 V
Output current I <sub>max.</sub>	≤ 100 mA
Response time	≤ 330 µs <sup>4)</sup>
Switching frequency	1,500 Hz <sup>5)</sup>
Output function	Complementary
Circuit protection	A <sup>6)</sup> C <sup>7)</sup> D <sup>8)</sup>

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

#### Mechanical data

Housing	Rectangular
Dimensions (W x H x D)	15.6 mm x 48.5 mm x 42 mm
Connection	Male connector M12, 4-pin
Material	
Housing	Metal
Front screen	Plastic, PMMA
Weight	120 g

# Ambient data

Enclosure rating	IP66 IP67
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

# Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904

 $<sup>^{2)}</sup>$  May not exceed or fall below  $U_{\nu}$  tolerances.

<sup>&</sup>lt;sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

 $<sup>^{6)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{7)}</sup>$  C = interference suppression.

 $<sup>^{8)}</sup>$  D = outputs overcurrent and short-circuit protected.


# WTB12-3P2413 | W12-3

SMALL PHOTOELECTRIC SENSORS

ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904
ECLASS 11.0	27270904
ECLASS 12.0	27270903
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

# Adjustments

WTB12-3, WTF12-3, double teach-in button



- 4 LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- ® Sensing range adjustment: double teach-in button

# Connection type




### Connection diagram

#### Cd-083

#### Characteristic curve


#### WTB12-3, infrared light



- $\ \, \textcircled{1}$  Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

# Sensing range diagram

#### WTB12-3, infrared light




#### Sensing range

- $\textcircled{\scriptsize 1}$  Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

#### Dimensional drawing (Dimensions in mm (inch))

WTB12-3, double teach-in button



- ① Standard direction of the material being detected
- ② Optical axis, receiver
- 3 Optical axis, sender
- ④ LED indicator green: Supply voltage active
- (5) LED indicator yellow: Status of received light beam
- 6 M4 threaded mounting hole, 4 mm deep
- 7 Mounting hole, Ø 4.2 mm
- Sensing range adjustment: double teach-in button
- Connection

#### Recommended accessories

Other models and accessories → www.sick.com/W12-3

	Brief description	Туре	Part no.	
Plug connect	Plug connectors and cables			
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PVC</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with chemicals</li> </ul>	YF2A14- 050VB3XLEAX	2096235	
	<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-G	6009932	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

