

## MZ2Q-TSLPSKQ0 MZ2Q-T

**SENSORS FOR T-SLOT CYLINDERS** 





### Ordering information

Туре	Part no.
MZ2Q-TSLPSKQ0	1042228

Other models and accessories → www.sick.com/MZ2Q-T



### Detailed technical data

### **Features**

Cylinder type	T-slot
Detection zone	0 mm 50 mm
Cylinder types with adapter	Profile cylinder Tie rod cylinder Round body cylinder Dovetail groove cylinder SMC rail CDQ2 SMC rail ECDQ2
Housing length	40 mm
Switching output	2 x PNP
Output function	NO
Electrical wiring	DC 4-wire
Enclosure rating	IP67 <sup>1)</sup>
IO-Link functions	Standard functions
Adjustment	
Teach-in control panel	Teaching in switching points 1 and 2
IO-Link	Disabling teach-in pushbutton Teaching in switching points 1 and 2 Tolerance band for switching points in 5 stages

<sup>&</sup>lt;sup>1)</sup> According to EN 60529.

### Mechanics/electronics

Detection zone	0 mm 50 mm

 $<sup>^{1)}\,\</sup>mbox{Supply}$  voltage  $\mbox{U}_{\mbox{\footnotesize B}}$  and constant ambient temperature Ta.

Supply voltage	15 V DC 30 V DC
Power consumption	Typ. 25 mA, without load
Voltage drop	≤ 2.2 V
Continuous current I <sub>a</sub>	≤ 100 mA
Protection class	III
Hysteresis, typ.	1 mT
Reproducibility	$\leq$ 0.1 mT $^{1)}$
Reverse polarity protection	Yes
Short-circuit protection	Yes
Status indicator LED	Yes
Teach-in	Yes
Power-up pulse protection	Yes
Ambient operating temperature	-20 °C +75 °C
Shock and vibration resistance	30 g, 11 ms / 10 55 Hz, 1 mm
EMC	According to EN 60947-5-2
Connection type	Cable with connector M12, 4-pin, with knurled nuts, 0.3 m
Connection type Detail	
Cable diameter	Ø 2.6 mm
Bending radius	With fixed installation $> 5 x$ cable diameter For flexible use $> 10 x$ cable diameter
Cable outlet	Axial
Material	
Housing	Plastic
Cable	PUR
UL File No.	NRKH.E181493 & NRKH7.E181493

 $<sup>^{1)}\,\</sup>mbox{Supply}$  voltage  $\mbox{U}_{\mbox{\footnotesize B}}$  and constant ambient temperature Ta.

### Safety-related parameters

MTTFD	799 years
DC <sub>avg</sub>	0%
T <sub>M</sub> (mission time)	20 years

### Communication interface

Communication interface	IO-Link V1.0
Communication Interface detail	COM2 (38,4 kBaud)
Cycle time	2.3 ms
Process data length	2 Bit
Process data structure	Bit 0 = switching signal $Q_{L1}$ Bit 1 = switching signal $Q_{L2}$ Bit 2 7 = empty

### Classifications


ECLASS 5.0	27270104
ECLASS 5.1.4	27270104

# MZ2Q-TSLPSKQ0 | MZ2Q-T SENSORS FOR T-SLOT CYLINDERS

ECLASS 6.0	27270104
ECLASS 6.2	27270104
ECLASS 7.0	27270104
ECLASS 8.0	27270104
ECLASS 8.1	27270104
ECLASS 9.0	27270104
ECLASS 10.0	27270104
ECLASS 11.0	27270104
ECLASS 12.0	27274301
ETIM 5.0	EC002544
ETIM 6.0	EC002544
ETIM 7.0	EC002544
ETIM 8.0	EC002544
UNSPSC 16.0901	39122230

### Installation note

Use the enclosed Teach-in-tool! See operating instructions.



### Connection type




### Connection diagram

Cd-244

### Dimensional drawing (Dimensions in mm (inch))

Cable with connector M12, with knurled nuts



- ① Fixing screw SW 1.5
- ② Display LED
- Teach-in button
- ④ Display LED
- ⑤ Connection

Part no.	Туре	L	Number of cores
1041323	MZ2Q-FTZPS-KQ0	300 mm	4
1042228	MZ2Q-TSLPSKQ0	300 mm	4
1062172	MZ2Q-TFSPSKQD	800 mm	4

### Recommended accessories

Other models and accessories → www.sick.com/MZ2Q-T

	Brief description	Туре	Part no.	
Fieldbus mod	Fieldbus modules			
	EtherCAT IO-Link Master, IO-Link V1.1, Port Class A, power supply via $7/8$ " cable 24 V / 8 A, fieldbus connection via M12 cable	IOLG2EC-03208R01 (IO-Link Master)	6053254	
	PROFINET IO-Link Master, IO-Link V1.1, Port Class A, power supply via $7/8$ " cable 24 V / 8 A, fieldbus connection via M12 cable	IOLG2PN-03208R01 (IO-Link Master)	6053253	

	Brief description	Туре	Part no.		
Brackets for c	Brackets for cylinder sensors				
	Mounting bracket for cylinder with dovetail slot, Aluminum, without mounting hardware	BEF-KHZ-ST1	2022703		
	Mounting bracket for integrated profile cylinder/tie-rod cylinder, zinc diecast, mounting hardware included	BEF-KHZ-PT1	2022702		
*	1 piece, Mounting bracket on round body cylinder with piston diameter of 12 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-12	2077681		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 16 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-16	2077680		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 20 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-20	2077679		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 25 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-25	2077678		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 32 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-32	2077677		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 40 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-40	2077676		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 50 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-50	2077675		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 63 mm, ambient temperature min 0 °C max 50 °C, plastic, Aluminum	BEF-KHZ-RT-63	2077674		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 130 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Zinc cast	BEF-KHZ-RT1-130	2077684		
THE STATE OF THE S	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 25 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Zinc cast	BEF-KHZ-RT1-25	2077682		
	1 piece, Mounting bracket on round body cylinder with piston diameter of 8 mm 63 mm, ambient temperature min –30 °C max 80 °C, stainless steel, Zinc cast	BEF-KHZ-RT1-63	2077683		
	Mounting bracket for mounting on SMC rails CDQ2 (T-slot), Aluminum, without mounting hardware	BEF-KHZ-TT2	2046440		
	Mounting bracket for mounting on SMC rails ECDQ2 (T-slot), Aluminum, without mounting hardware	BEF-KHZ-TT1	2046439		
Plug connecto	ors and cables				
No.	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A14- 020UB3XLEAX	2095607		
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, straight, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YF2A14- O5OUB3XLEAX	2095608		
	<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YG2A14- 020UB3XLEAX	2095766		

Brief description	Туре	Part no.
<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YG2A14- 050UB3XLEAX	2095767
<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 2 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YI2A14- 020UB3XLEAX	2095836
<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled, A-coded</li> <li>Connection type head B: Flying leads</li> <li>Signal type: Sensor/actuator cable</li> <li>Cable: 5 m, 4-wire, PUR, halogen-free</li> <li>Description: Sensor/actuator cable, unshielded, LED function display</li> <li>Note: Only suitable for PNP sensors</li> <li>Application: Zones with oils and lubricants, Drag chain operation, Robot</li> </ul>	YI2A14- 050UB3XLEAX	2095837
Connection type head A: Female connector, M12, 4-pin, straight     Description: Unshielded, Head A: female connector, M12, 4-pin, straight, unshielded, for power supply, for cable diameter 4 mm 6 mm Head B: -     Connection systems: Screw-type terminals     Permitted cross-section: ≤ 0.75 mm²	DOS-1204-G	6007302
<ul> <li>Connection type head A: Female connector, M12, 4-pin, angled</li> <li>Description: Unshielded, Head A: female connector, M12, 4-pin, angled, unshielded, for power supply, for cable diameter 3 mm 6.5 mm Head B: -</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	DOS-1204-W	6007303
<ul> <li>Connection type head A: Male connector, M12, 4-pin, straight</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-G	6009932
<ul> <li>Connection type head A: Male connector, M12, 4-pin, angled</li> <li>Description: Unshielded</li> <li>Connection systems: Screw-type terminals</li> <li>Permitted cross-section: ≤ 0.75 mm²</li> </ul>	STE-1204-W	6022084

### Recommended services

Additional services → www.sick.com/MZ2Q-T

	Туре	Part no.
Function Block Factory		
<ul> <li>Description: The Function Block Factory supports common programmable logic controllers (PLCs) from various manufacturers, such as Siemens, Beckhoff, Rockwell Automation and B&amp;R. More information on the FBF can be found <a href="https://fbf.cloud.sick.com" target="_blank"> here</a>.</li> <li>Note: You can configure your function block at <a href="https://fbf.cloud.sick.com" target="_blank"> Function Block Factory.</a> As a login please use your SICK ID.</li> </ul>	Function Block Factory	On request

### SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

### **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

