

WTB4S-3P2231

MINIATURE PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WTB4S-3P2231	1042057

Other models and accessories → www.sick.com/W4

Illustration may differ





Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Sensing range max.	4 mm 120 mm ¹⁾
Sensing range	10 mm 120 mm ¹⁾
Emitted beam	
Light source	PinPoint LED ²⁾
Type of light	Visible red light
Light spot size (distance)	Ø 2.5 mm (50 mm)
Key LED figures	
Wave length	650 nm
Adjustment	Potentiometer, 5 turns

 $^{^{1)}}$ Object with 90% remission (based on standard white, DIN 5033).

Safety-related parameters

MTTF _D	1,023 years
DC _{avg}	0 %

 $^{^{2)}}$ Average service life: 100,000 h at TU = +25 °C.

Electrical data

Supply voltage \mathbf{U}_{B}	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	20 mA ³⁾
Protection class	III
Digital output	
Туре	PNP
Switching mode	Light/dark switching
Output current I _{max.}	≤ 100 mA
Response time	< 0.5 ms ⁴⁾
Switching frequency	1,000 Hz ⁵⁾
Circuit protection	A ⁶⁾ C ⁷⁾ D ⁸⁾

¹⁾ Limit values.

Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	12.2 mm x 41.8 mm x 17.3 mm
Connection	Male connector M8, 4-pin
Material	
Housing	Plastic, ABS
Front screen	Plastic, PMMA
Weight	30 g

Ambient data

Enclosure rating	IP67 IP66
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.

⁸⁾ D = outputs overcurrent and short-circuit protected.

WTB4S-3P2231 | W4

MINIATURE PHOTOELECTRIC SENSORS

ECLASS 8.0 27270904	
ECLASS 8.1 27270904	
ECLASS 9.0 27270904	
ECLASS 10.0 27270904	
ECLASS 11.0 27270904	
ECLASS 12.0 27270903	
ETIM 5.0 EC002719	
ETIM 6.0 EC002719	
ETIM 7.0 EC002719	
ETIM 8.0 EC002719	
UNSPSC 16.0901 39121528	

Connection type




Connection diagram

Cd-083

Characteristic curve


WTB4S-3, 120 mm

% of sensing distance




- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor③ Sensing range on white, 90% remission factor

Light spot size



Sensing range diagram


WTB4S-3, 120 mm



- Sensing range max.
- Sensing range
- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

Dimensional drawing (Dimensions in mm (inch))

WTB4S-3, potentiometer



- ① Standard direction of the material being detected
- ② Optical axis, receiver
- 3 Optical axis, sender
- ④ LED indicator green: Supply voltage active
- ⑤ LED indicator yellow: Status of received light beam
- 6 Potentiometer
- Threaded mounting hole M3
- ® Connection

Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.	
Mounting bra	Mounting brackets and plates			
le le	Mounting bracket for wall mounting, Stainless steel 1.4571, mounting hardware included	BEF-W4-A	2051628	
Plug connecto	Plug connectors and cables			
	 Connection type head A: Female connector, M8, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF8U14- 050VA3XLEAX	2095889	
	 Connection type head A: Male connector, M8, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: 0.14 mm² 0.5 mm² 	STE-0804-G	6037323	

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

