

WL4S-3F2132V W4

**MINIATURE PHOTOELECTRIC SENSORS** 





## Ordering information

Туре	Part no.
WL4S-3F2132V	1046428

Other models and accessories → www.sick.com/W4

Illustration may differ





### Detailed technical data

### **Features**

i catares	
Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Sensing range max.	0 m 5 m <sup>1)</sup>
Sensing range	0 m 3 m <sup>1)</sup>
Polarisation filters	Yes
Emitted beam	
Light source	PinPoint LED <sup>2)</sup>
Type of light	Visible red light
Light spot size (distance)	Ø 45 mm (1.5 m)
Key LED figures	
Wave length	650 nm
Adjustment	Single teach-in button
Special applications	Hygienic and washdown zones
Housing design	Washdown

<sup>&</sup>lt;sup>1)</sup> Reflector PL80A.

## Safety-related parameters

MTTF <sub>D</sub>	1,770 years
DC <sub>avg</sub>	0 %

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at TU = +25 °C.

### Electrical data

Supply voltage $\mathbf{U}_{\mathrm{B}}$	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Protection class	III
Digital output	
Туре	PNP
Switching mode	Dark switching
Output current I <sub>max.</sub>	≤ 100 mA
Response time	< 0.5 ms <sup>4)</sup>
Switching frequency	1,000 Hz <sup>5)</sup>
Circuit protection	A, B, C <sup>6) 7) 8)</sup>

<sup>&</sup>lt;sup>1)</sup> Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

### Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	15.25 mm x 44.9 mm x 22.2 mm
Connection	Connector M8, 3-pin <sup>1)</sup>
Material	
Housing	Stainless steel, Stainless steel V4A (1.4404, 316L)
Front screen	Plastic, PMMA
Weight	40 g

<sup>1)</sup> Max. tightening torque: 0.6 Nm.

### Ambient data

Enclosure rating	IP66 IP67 IP68 IP69K <sup>1)</sup>
Ambient operating temperature	-30 °C +70 °C <sup>2)</sup> -30 °C +60 °C
Ambient temperature, storage	-30 °C +75 °C
UL File No.	NRKH.E181493 & NRKH7.E181493

 $<sup>^{1)}\,\</sup>mathrm{Only}$  in case of correctly mounted IP69K connecting cable.

 $<sup>^{2)}</sup>$  May not exceed or fall below  $\mathrm{U}_{\mathrm{V}}$  tolerances.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Signal transit time with resistive load.

<sup>5)</sup> With light/dark ratio 1:1.

<sup>6)</sup> A = V<sub>S</sub> connections reverse-polarity protected.

<sup>&</sup>lt;sup>7)</sup> B = inputs and output reverse-polarity protected.

 $<sup>^{8)}</sup>$  C = interference suppression.

 $<sup>^{2)}</sup>$  At UV  $\leq$  24 V and IA < 30 mA.

## Classifications


ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

## Connection type



## Connection diagram


## Cd-045



#### Characteristic curve

WL4S-3, WLG4S-3, 5 m


#### Operating reserve



- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- 4 PL10F reflector
- ⑤ Reflector P250 CHEM
- ® Reflective tape REF-IRF-56

### Sensing range diagram


WL4S-3, WLG4S-3, 5 m





- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- 4 PL10F reflector
- ⑤ Reflector P250 CHEM
- ® Reflective tape REF-IRF-56


### Dimensional drawing (Dimensions in mm (inch))

WL4S-3V, WLG4S-3V, with single teach-in button









- ① Center of optical axis
- ② Threaded mounting hole M3
- 3 LED indicator yellow: Status of received light beam
- 4 LED indicator green: Supply voltage active
- ⑤ Teach-in button

### Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.
Mounting brackets and plates			
A A	Mounting bracket for floor mounting, Stainless steel 1.4571, mounting hardware included	BEF-W4-B	2051630
Reflectors			
==	Chemically resistant, screw connection, 52 mm x 61 mm, plastic, Screw-on, 2 hole mounting	P250 CHEM	5321097

	Brief description	Туре	Part no.
Others			
6	Connection type head A: Female connector, M8, 3-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 3-wire, PP Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB) and other chemical compounds such as H2O2 and CH2O2. Before permanent installation is carried out, the material's resistance to the cleaning agent being used must be checked., Resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones, Drag chain operation	DOL-0803-G05MRN	6058505

## SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

