



MINIATURE PHOTOELECTRIC SENSORS

SICKSensor Intelligence.



Ordering information

Туре	Part no.
WLG4S-3P3232H	1048120

Other models and accessories → www.sick.com/W4

Illustration may differ





Detailed technical data

Features

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Sensing range max.	0 m 5 m ¹⁾
Sensing range	0 m 3 m ¹⁾
Polarisation filters	Yes
Emitted beam	
Light source	PinPoint LED ²⁾
Type of light	Visible red light
Light spot size (distance)	Ø 45 mm (1.5 m)
Key LED figures	
Wave length	650 nm
Adjustment	Single teach-in button
Special applications	Hygienic and washdown zones, Detecting transparent objects
Housing design	Hygiene
AutoAdapt	✓

¹⁾ Reflector PL80A.

Safety-related parameters

MTTF _D	1,215 years
-------------------	-------------

 $^{^{2)}}$ Average service life: 100,000 h at T_{U} = +25 $^{\circ}\text{C}.$

DC _{avg}	0 %
T _M (mission time)	20 years

Electrical data

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	30 mA ³⁾
Protection class	III
Digital output	
Туре	PNP
Switching mode	Light/dark switching
Output current I _{max.}	≤ 100 mA
Response time	< 0.5 ms ⁴⁾
Switching frequency	1,000 Hz ⁵⁾
Attenuation along light beam	> 8 %
Output function	Complementary
Circuit protection	A, B, C ^{6) 7) 8)}

 $^{^{1)}}$ Limit values, reverse-polarity protected, operation in short-circuit protected network: max. 8 A.

Mechanical data

Housing	Rectangular
Design detail	Slim
Dimensions (W x H x D)	15.25 mm x 63.2 mm x 22.15 mm
Connection	Cable with M8 male connector, 4-pin ^{1) 2)}
Connection detail	
Length of cable (L)	150 mm ²⁾
Material	
Housing	Stainless steel, Stainless steel V4A (1.4404, 316L)
Front screen	Plastic, PMMA
Cable	PVC
Weight	50 g

¹⁾ Max. tightening torque: 0.6 Nm.

Ambient data

Enclosure rating	IP66 IP67

 $^{^{1)}}$ At UV \leq 24 V and IA < 30 mA.

 $^{^{2)}\,\}mathrm{May}$ not exceed or fall below U_{V} tolerances.

³⁾ Without load.

 $^{^{4)}}$ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

 $^{^{7)}}$ B = inputs and output reverse-polarity protected.

⁸⁾ C = interference suppression.

²⁾ Do not bend below 0 °C.

	IP68 IP69K
Ambient operating temperature	-30 °C +70 °C ¹⁾ -30 °C +60 °C
Ambient temperature, storage	-30 °C +75 °C
UL File No.	FDA, UL No. NRKH.E181493 & cUL No. NRKH7.E181493

 $^{^{1)}}$ At UV \leq 24 V and IA < 30 mA.

Classifications

ECLASS 5.0	27270902
ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

Connection type




Connection diagram

Cd-083

Characteristic curve

WL4S-3, WLG4S-3, 5 m


Operating reserve



- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- 4 PL10F reflector
- ⑤ Reflector P250 CHEM
- ® Reflective tape REF-IRF-56

Sensing range diagram


WL4S-3, WLG4S-3, 5 m



- Sensing range
- Sensing range max.
- ① Reflector PL80A
- ② Reflector PL40A
- 3 Reflector PL20A
- 4 PL10F reflector
- ⑤ Reflector P250 CHEM
- ® Reflective tape REF-IRF-56

Dimensional drawing (Dimensions in mm (inch))

WL4S-3H, WLG4S-3H, with single teach-in button



- ① Center of optical axis
- ② Sealing ring (tightening torque 6 Nm)
- 3 Connector M12
- ④ LED indicator yellow: Status of received light beam
- ⑤ LED indicator green: Supply voltage active
- 6 Teach-in button

Recommended accessories

Other models and accessories → www.sick.com/W4

	Brief description	Туре	Part no.
Other mounting accessories			
	Diameter 18 mm x 100 mm for W4S-3 Inox hygiene. Hygienic integration without holes and brackets. Cable run inside tube	BEF-MR18G-NA	4065853
Reflectors			
==	Chemically resistant, screw connection, $52\ \text{mm}\ \text{x}\ 61\ \text{mm}$, plastic, Screw-on, $2\ \text{hole}$ mounting	P250 CHEM	5321097

	Brief description	Туре	Part no.
Others			
	Connection type head A: Female connector, M8, 4-pin, straight Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Connection systems: Flying leads Note: This product is generally resistant to chemical cleaning agents (see ECOLAB). Please do not use cleaning agents of any other Kind., Not resistant against lactic acid & hydrogen peroxide (H2O2) Application: Hygienic and washdown zones	DOL-0804-G05MNI	6059194

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

