



Ranger-E55434

Ranger

3D MACHINE VISION

SICK
Sensor Intelligence.



Ordering information

Type	part no.
Ranger-E55434	1050268

Other models and accessories → www.sick.com/Ranger



Detailed technical data

Features

Task	Color inspection Quality inspection, high-speed Measuring, 3D
Technology	3D line scanning, MultiScan, color
Product category	Streaming, flexible
Example field of view	Free of choice by lens selection
Illumination	To be ordered separately as accessories
Data synchronization	Free running, encoder triggered, external triggering
Grayscale measurements	✓
Scatter measurement	✓
Color measurements	Red, Green, blue, monochrome (without IR content)
Spectral range	400 nm ... 950 nm
Description	ColorRanger E55 - 3D and RGB color with MultiScan at up to 11 kHz (3D and color data). Giga-bit Ethernet interface, 1,536 px 3D resolution, 3 px x 3,072 px RGB color resolution.
Lens	C-mount
Optical format	1"

Mechanics/electronics

Connection type	Power I/O: M12, 8-pin male M12, 8-pin female connector (encoder) RJ45 (Ethernet)
Connector material	M12: nickel-plated brass
Supply voltage	12 V DC ... 24 V DC
Ripple	< 5 V _{pp}
Power consumption	7 W
Current consumption	0.8 A
Standards (ROHS)	✓
Enclosure rating	IP20
Housing material	Aluminum
Housing color	Gray, varnished
Weight	360 g
Dimensions (L x W x H)	125 mm x 52 mm x 52 mm

Performance

Bit depth	8 bit
Image sensor	CMOS
Sensor resolution	1,536 px x 512 px
Scan/frame rate	35,000 3D profiles/s
Maximum color performance	13,000 RGB lines/second
Maximum 3D and color rate	11,000 Scans/second
Maximum Hi-Res color rate	10,000 RGB lines/second
Sensor rows available for 3D	35 ... 511
3D profile resolution	1,536 px
Scatter resolution	1,536 px
Color resolution	3 x 3,072 px
Pixel size	9.5 µm x 9.5 µm
Standard color row pitch	38 µm
Pixel matrix fill factor	60 %
Maximum 3D height resolution	13 bits 1/16 pixels
Optical center (row, column)	(227, 768)
Gray-scale resolution	3,072 px
IR filter	No IR pass filter
Hi-res pixel size (H x V)	4.75 µm x 9.5 µm
Hi-res pixel fill factor	80 %
Hi-res color pixel size (H x V)	4.75 µm x 20 µm
Hi-res color line spacing	42 µm

Interfaces

Ethernet	✓ , UDP/IP
Data transmission rate	1,000 Mbit/s
Serial	✓ , RS-422
Function	Encoder
Data transmission rate	Maximum encoder frequency: 2 MHz
Configuration software	Ranger Studio
Operating system	Windows XP Pro, Windows 7
Development environment	C++ (VS 2005/2008/2010) / C
Programming interface	iCon API
Digital input	4 x HIGH = 10 V ... 28.8 V
Digital output	1 x TTL level, 2 x B-type, < 100 mA in total
Encoder interface	RS-422
Maximum encoder frequency	2 MHz
External illumination	5 V TTL

Ambient data

Shock load	15 g, 3 x 6 directions
-------------------	------------------------

¹⁾ Non-condensing.

Vibration load	5 g, 58 Hz ... 150 Hz
Ambient operating temperature	0 °C ... +45 °C ¹⁾
Storage temperature	-20 °C ... +70 °C ¹⁾

¹⁾ Non-condensing.


Certificates

EU declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓

Classifications

ECLASS 5.0	27310205
ECLASS 5.1.4	27310205
ECLASS 6.0	27310205
ECLASS 6.2	27310205
ECLASS 7.0	27310205
ECLASS 8.0	27310205
ECLASS 8.1	27310205
ECLASS 9.0	27310205
ECLASS 10.0	27310205
ECLASS 11.0	27310205
ECLASS 12.0	27310205
ETIM 5.0	EC001820
ETIM 6.0	EC001820
ETIM 7.0	EC001820
ETIM 8.0	EC001820
UNSPSC 16.0901	43211731

dimensional drawing, view from below




Dimensions in mm (inch)

① Mounting holes M5, 9 mm (2 x)


② Mounting holes M3, 3 mm (4 x per side)

dimensional drawing, view from the side




Dimensions in mm (inch)
② Mounting holes M3, 3 mm (4 x per side)


Characteristic curves, speed characteristics




Hi-res color sensitivity




Standard color response




Connection type



Connection diagram, voltage I/O



Connection diagram, encoder connection



Recommended accessories

Other models and accessories → www.sick.com/Ranger

	Brief description	Type	part no.
reflectors and optics			
	<ul style="list-style-type: none">• Description: Laser module with line projecting lens (red, 35 mW, refocusable), with open wires• Light source: Laser, red• Connection types: Cable, 1,000 mm, open wires	Ranger accessories, laser	6033005

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com