



FX3-ANA020002

Flexi Soft

SAFETY CONTROLLERS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
FX3-ANA020002	1051134

Other models and accessories → www.sick.com/Flexi_Soft



Detailed technical data

Features

Module	Analog input module
Configuration method	Via software (Flexi Soft Designer)

Safety-related parameters

Safety integrity level	SIL 3 (IEC 61508)
Category	Category 4 (EN ISO 13849)
Performance level	PL e (EN ISO 13849)
PFH_D (mean probability of a dangerous failure per hour)	0.166 x 10 ⁻⁹
T_M (mission time)	20 years (EN ISO 13849-1)

Functions

Limit value monitoring	✓
Signal range detection	✓

Interfaces

Number of safe analog inputs	2
Connection type	Plug-in spring terminals

Electronics

Protection class	III (EN 61140)
Voltage supply	Via FLEXBUS+

¹⁾ Via FLEXBUS+, without streams at analog inputs.

²⁾ Threshold below which a sensor fault is assumed. A max. deviation of 1% (full scale value) gives a tolerance range of 3.3 mA to 3.7 mA.

³⁾ Threshold above which a sensor fault is assumed. A max. deviation of 1% (full scale value) gives a tolerance range of 20.3 mA to 20.7 mA.

Internal power consumption	≤ 2 W ¹⁾
Analogue inputs	
Input voltage	≤ 30 V DC
Input current	≤ 30 mA
Current measuring range	4 mA ... 20 mA
Current input measuring range	3.5 mA ... 20.5 mA ^{2) 3)}
Input resistance	50 Ω

¹⁾ Via FLEXBUS+, without streams at analog inputs.

²⁾ Threshold below which a sensor fault is assumed. A max. deviation of 1% (full scale value) gives a tolerance range of 3.3 mA to 3.7 mA.

³⁾ Threshold above which a sensor fault is assumed. A max. deviation of 1% (full scale value) gives a tolerance range of 20.3 mA to 20.7 mA.

Mechanics

Dimensions (W x H x D)	22.5 mm x 96.5 mm x 120.6 mm
Weight	117 g (± 5 %)

Ambient data

Enclosure rating	IP20 (EN 60529)
Ambient operating temperature	-25 °C ... +55 °C
Storage temperature	-25 °C ... +70 °C
Air humidity	≤ 95 %, Non-condensing

Certificates


EU declaration of conformity	✓
UK declaration of conformity	✓
ACMA declaration of conformity	✓
China RoHS	✓
CCC certificate	✓
UK-Type-Examination approval	✓
cULus certificate	✓
cTUVus certificate	✓
S Mark certificate	✓
EC-Type-Examination approval	✓
Information according to Art. 3 of Data Act (Regulation EU 2023/2854)	✓

Classifications

ECLASS 5.0	27243001
ECLASS 5.1.4	27243101
ECLASS 6.0	27243101
ECLASS 6.2	27243101
ECLASS 7.0	27243101
ECLASS 8.0	27243101
ECLASS 8.1	27243101
ECLASS 9.0	27243101
ECLASS 10.0	27243101

ECLASS 11.0	27243101
ECLASS 12.0	27243101
ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449
ETIM 8.0	EC001449
UNSPSC 16.0901	32151705



Dimensional drawing FX3-ANA0



Dimensions in mm (inch)

Recommended accessories

Other models and accessories → www.sick.com/Flexi_Soft

	Brief description	Type	part no.
Safety relays			
	<ul style="list-style-type: none"> • Applications: Output expansion module for OSSDs • Compatible sensor types: Safety sensors with OSSDs • Connection type: Front connector with spring terminals • Restart interlock: no • External device monitoring (EDM): Via path • Outputs: 4 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe), 1 signaling current path (not safe) • Housing width: 28 mm 	RLY3-OSSD400	1099971
	<ul style="list-style-type: none"> • Applications: Output expansion module for OSSDs • Compatible sensor types: Safety sensors with OSSDs • Connection type: Front connector with spring terminals • Restart interlock: no • External device monitoring (EDM): Via path • Outputs: 2 enabling current paths (safe), 1 feedback current path (for use as external device monitoring, not safe) • Housing width: 18 mm 	RLY3-OSSD100	1085343

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com