

LMC133-11101 VdS

LMC1xx

2D LIDAR SENSORS





Ordering information

Туре	part no.
LMC133-11101 VdS	1051489

Other models and accessories → www.sick.com/LMC1xx



Detailed technical data

Features

Application	Security, Outdoor, Indoor
Light source	Infrared (905 nm)
Laser class	1 (IEC 60825-1:2014, EN 60825-1:2014+A11:2021)
Aperture angle	
Horizontal	270°
Scanning frequency	50 Hz
Angular resolution	
Horizontal	0.25°
	0.5°
Heating	Yes
Working range	0.5 m 20 m
Scanning range	
At 10% remission factor	18 m
Amount of evaluated echoes	2

Mechanics/electronics

Connection type	1 x M12 round connector
Supply voltage	9 V DC 30 V DC
Power consumption	Typ. 8 W, 20 W, heating typ. 35 W
Housing color	Signal white (RAL 9003)
Enclosure rating	IP67 (EN 60529, Section 14.2.5)
Protection class	III (EN 50178 (1997;10))
Weight	1.1 kg, without connecting cables
Dimensions (L x W x H)	105 mm x 102 mm x 152 mm
МТВБ	> 100 years

Safety-related parameters

MTTF _D	> 100 years

Performance

Response time	≥ 20 ms
Detectable object shape	Almost any
Systematic error	± 30 mm ¹⁾
Statistical error	12 mm ¹⁾
Integrated application	Field evaluation Security conform parameterization
Number of field sets	10 fields
Simultaneous evaluation cases	10

 $^{^{1)}\,\}mbox{Typical}$ value; actual value depends on environmental conditions.

Interfaces

Ethernet	✓, TCP/IP
Function	Data interface (read result output)
Data transmission rate	10/100 MBit/s
Serial	√ , RS-232
Function	Data interface (read result output), Service interface
Data transmission rate	9.6 kBaud 115.2 kBaud
CAN	✓
Function	Extension of outputs
Digital inputs/outputs	
Inputs	4 digital
Outputs	3 (2 relay, 1 digital)
Optical indicators	17-segment display (plus 5 LEDs showing device status, contamination warning and initial condition, both can be activated)

Ambient data

Object remission	2 % > 1,000 % (reflectors)
Electromagnetic compatibility (EMC)	EN 61000-6-2:2005 / EN 61000-6-4 (2007-01)
Vibration resistance	EN 60068-2-6 (1995-04)
Shock resistance	EN 60068-2-27 (1993-03)
Ambient operating temperature	-30 °C +50 °C
Storage temperature	-30 °C +70 °C
Ambient light immunity	40,000 lx

General notes

Items supplied	LMS13x VdS (Outdoor), Mounting protection bracket VdS 2 (short)
Note on use	The sensor does not constitute a safety component as defined by relevant legislation on machine safety.

Classifications


ECLASS 5.0	27270990
ECLASS 5.1.4	27270990

LMC133-11101 VdS | LMC1xx

2D LIDAR SENSORS

ECLASS 6.0	27270913
ECLASS 6.2	27270913
ECLASS 7.0	27270913
ECLASS 8.0	27270913
ECLASS 8.1	27270913
ECLASS 9.0	27270913
ECLASS 10.0	27270913
ECLASS 11.0	27270913
ECLASS 12.0	27270913
ETIM 5.0	EC002550
ETIM 6.0	EC002550
ETIM 7.0	EC002550
ETIM 8.0	EC002550
UNSPSC 16.0901	41111615

Working range diagram



Scanning range for objects up to 10 % remission 18 m (59.06 ft)


Connection type Ethernet



M12 female connector, 4-pin, D-coded

- ① TX+
- ② RX+
- ③ TX-
- 4 RX-


PIN assignment "data" connection



M12 male connector, 8-pin, A-coded

- ① RxD (HOST)
- ② TxD (HOST)
- 3 CAN_H
- 4 CAN_L
- **⑤** GND RS/CAN
- 6 In₁
- ⑦ In₂
- **® GND IN1/2**

PIN assignment I/O connection



female connector M12, 8-pin, A-coded

- ① LMS11x: INC1 A / LMS15x/LMS16x: INC1 A or IN4 (switchable, pins 1 and 2 must be switched together)
- ② LMS11x: INC1 B / LMS15x/LMS16x: INC1 B or IN3 (switchable, pins 1 and 2 must be switched together)
- 3 GND INC1
- ④ OUT1 A
- ⑤ OUT2 A
- ⑥ OUT3 A
- ⑦ OUT1 ... 3 B
- ® 0UT1 ... 3 R

PIN assignment Service interface



female connector M8, 4-pin

- ① Reserved
- ② RxD AUX
- ③ GND RS
- ④ TxD AUX

LMC133-11101 VdS | LMC1xx

2D LIDAR SENSORS

PIN assignment Power



Connector M12, 5-pin, A-coded

- \bigcirc V_s
- ② V_s heat.
- ③ GND
- ④ Reserved
- ⑤ GND heat.

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

