

WL9M4-3P3432 w9

**SMALL PHOTOELECTRIC SENSORS** 





# Ordering information

Туре	Part no.
WL9M4-3P3432	1051907

Other models and accessories → www.sick.com/W9

Illustration may differ



### Detailed technical data

### **Features**

Functional principle	Photoelectric retro-reflective sensor
Functional principle detail	Autocollimation
Dimensions (W x H x D)	12.2 mm x 50 mm x 23.6 mm
Housing design (light emission)	Rectangular
Mounting hole	M4
Sensing range max.	0 m 5 m <sup>1)</sup>
Sensing range	0 m 3 m <sup>1)</sup>
Type of light	Visible red light
Light source	PinPoint LED <sup>2)</sup>
Light spot size (distance)	Ø 45 mm (1.5 m)
Wave length	650 nm
Adjustment	Single teach-in button
Special applications	Detecting small objects

<sup>&</sup>lt;sup>1)</sup> Reflector PL80A.

 $<sup>^{2)}</sup>$  Average service life: 100,000 h at  $T_{U}$  = +25 °C.

### Mechanics/electronics

Wiconamos, cicotromos	
Supply voltage U <sub>B</sub>	10 V DC 30 V DC <sup>1)</sup>
Ripple	< 5 V <sub>pp</sub> <sup>2)</sup>
Current consumption	30 mA <sup>3)</sup>
Switching output	PNP <sup>4)</sup>
Output function	Complementary
Switching mode	Light/dark switching <sup>4)</sup>
Output current I <sub>max.</sub>	$\leq$ 100 mA $^{5)}$
Response time	< 0.5 ms <sup>6)</sup>
Switching frequency	1,000 Hz <sup>7)</sup>
Connection type	Cable with M12 male connector, 4-pin, 120 mm <sup>8)</sup>
Cable material	PVC
Conductor cross section	0.14 mm <sup>2</sup>
Circuit protection	A <sup>9)</sup> B <sup>10)</sup> C <sup>11)</sup>
Protection class	III
Weight	80 g
Polarisation filter	✓
Housing material	Plastic, VISTAL®
Optics material	Plastic, PMMA
Enclosure rating	IP66 IP67 IP69K
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C
UL File No.	NRKH.E181493

 $<sup>^{1)}</sup>$  Limit values when operated in short-circuit protected network: max. 8 A.

## Safety-related parameters

MTTF <sub>D</sub>	1,668 years
DC <sub>avg</sub>	0 %
T <sub>M</sub> (mission time)	20 years

#### Classifications

ECLASS 5.0	27270902
------------	----------

 $<sup>^{2)}\,\</sup>mbox{May}$  not exceed or fall below  $\mbox{U}_{\mbox{\scriptsize V}}$  tolerances.

<sup>3)</sup> Without load.

 $<sup>^{4)}</sup>$  Q = light switching.

 $<sup>^{5)}</sup>$  At and above Tu 50 °C, a max. load current of Imax. = 50 mA is permitted.

 $<sup>^{6)}</sup>$  Signal transit time with resistive load.

<sup>7)</sup> With light/dark ratio 1:1.

<sup>8)</sup> Do not bend below 0 °C.

 $<sup>^{9)}</sup>$  A = V<sub>S</sub> connections reverse-polarity protected.

 $<sup>^{10)}</sup>$  B = inputs and output reverse-polarity protected.

 $<sup>^{11)}</sup>$  C = interference suppression.


# WL9M4-3P3432 | W9

### SMALL PHOTOELECTRIC SENSORS

ECLASS 5.1.4	27270902
ECLASS 6.0	27270902
ECLASS 6.2	27270902
ECLASS 7.0	27270902
ECLASS 8.0	27270902
ECLASS 8.1	27270902
ECLASS 9.0	27270902
ECLASS 10.0	27270902
ECLASS 11.0	27270902
ECLASS 12.0	27270902
ETIM 5.0	EC002717
ETIM 6.0	EC002717
ETIM 7.0	EC002717
ETIM 8.0	EC002717
UNSPSC 16.0901	39121528

### Adjustments

Single teach-in button



- $\ensuremath{\mathfrak{G}}$  LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- ® Teach-in button

# Connection type




### Connection diagram

Cd-084

#### Characteristic curve

WL9-3, red light, 5 m


Function reserve



- ① Reflector PL80A
- ② Reflector P250
- 3 Reflector PL40A
- 4 Reflector PL20A
- ⑤ PL10F reflector
- ® Reflective tape REF-IRF-56


### Light spot size

WL9-3, red light, 5 m



### Sensing range diagram


WL9-3, red light, 5 m



- ① Reflector PL80A
- ② Reflector P250F
- ③ Reflector PL40A
- ④ Reflector PL20F
- ⑤ PL10F reflector
- ® Reflective tape REF-IRF-56

### Dimensional drawing (Dimensions in mm (inch))

WL9M4-3, WSE9M4-3



- ① Sender and receiver optical axis center
- ② Mounting hole M4 (Ø 4.1 mm)
- ③ LED indicator yellow: Status of received light beam
- 4 LED indicator green: power on
- ⑤ Connecting cable or connector
- Male connector M8, 4-pin
- 7 Male connector M12, 4-pin

### Recommended accessories

Other models and accessories → www.sick.com/W9

	Brief description	Туре	Part no.	
Plug connectors and cables				
	Head A: female connector, M12, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF2A14- 050VB3XLEAX	2096235	
	Head A: female connector, M8, 4-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PVC, unshielded, 5 m	YF8U14- 050VA3XLEAX	2095889	
	Head A: male connector, M8, 4-pin, straight Cable: unshielded	STE-0804-G	6037323	
	Head A: male connector, M12, 4-pin, straight Cable: unshielded	STE-1204-G	6009932	
Reflectors				
	Fine triple reflector, screw connection, suitable for laser sensors, 20 mm x 32 mm, PM-MA/ABS, Screw-on, 2 hole mounting	PL10F	5311210	

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

